



PJP12NA60 / PJF12NA60

600V N-Channel MOSFET


Voltage	600 V	Current	12 A
----------------	--------------	----------------	-------------

Features

- $R_{DS(ON)}, V_{GS}@10V, I_D@6A < 0.7\Omega$
- High switching speed
- Improved dv/dt capability
- Low Gate Charge
- Low reverse transfer capacitance
- Lead free in compliance with EU RoHS 2011/65/EU directive.
- Green molding compound as per IEC61249 Std. (Halogen Free)

Mechanical Data

- Case : TO-220AB, ITO-220AB-F Package
- Terminals : Solderable per MIL-STD-750, Method 2026
- TO-220AB Approx. Weight : 0.067 ounces, 1.89 grams
- ITO-220AB-F Approx. Weight : 0.068 ounces, 2 grams



Maximum Ratings and Thermal Characteristics ($T_A=25^\circ\text{C}$ unless otherwise noted)

PARAMETER		SYMBOL	TO-220AB	ITO-220AB-F	UNITS
Drain-Source Voltage		V_{DS}	600		V
Gate-Source Voltage		V_{GS}	± 30		V
Continuous Drain Current		I_D	12		A
Pulsed Drain Current		I_{DM}	48		A
Single Pulse Avalanche Energy ^(Note 1)		E_{AS}	795		mJ
Power Dissipation	$T_C=25^\circ\text{C}$	P_D	225	51	W
	Derate above 25°C		1.8	0.41	W/ $^\circ\text{C}$
Operating Junction and Storage Temperature Range		T_J, T_{STG}	-55~150		$^\circ\text{C}$
Typical Thermal resistance					
-	Junction to Case	$R_{\theta JC}$	0.56	2.45	$^\circ\text{C/W}$
-	Junction to Ambient	$R_{\theta JA}$	62.5	120	

- Limited only By Maximum Junction Temperature



PJP12NA60 / PJF12NA60

Electrical Characteristics ($T_A=25^\circ\text{C}$ unless otherwise noted)

PARAMETER	SYMBOL	TEST CONDITION	MIN.	TYP.	MAX.	UNITS
Static						
Drain-Source Breakdown Voltage	BV_{DSS}	$V_{GS}=0V, I_D=250\mu A$	600	-	-	V
Gate Threshold Voltage	$V_{GS(th)}$	$V_{DS}=V_{GS}, I_D=250\mu A$	2	2.96	4	V
Drain-Source On-State Resistance	$R_{DS(on)}$	$V_{GS}=10V, I_D=6A$	-	0.59	0.7	Ω
Zero Gate Voltage Drain Current	I_{DSS}	$V_{DS}=600V, V_{GS}=0V$	-	0.02	1	μA
Gate-Source Leakage Current	I_{GSS}	$V_{GS}=\pm 30V, V_{DS}=0V$	-	± 10	± 100	nA
Diode Forward Voltage	V_{SD}	$I_S=12A, V_{GS}=0V$	-	0.85	1.4	V
Dynamic (Note 4)						
Total Gate Charge	Q_g	$V_{DS}=480V, I_D=12A,$ $V_{GS}=10V$ (Note 2,3)	-	24	-	nC
Gate-Source Charge	Q_{gs}		-	7.8	-	
Gate-Drain Charge	Q_{gd}		-	7.4	-	
Input Capacitance	C_{iss}	$V_{DS}=25V, V_{GS}=0V,$ $f=1.0\text{MHz}$	-	1492	-	pF
Output Capacitance	C_{oss}		-	167	-	
Reverse Transfer Capacitance	C_{rss}		-	4.5	-	
Turn-On Delay Time	$t_{d(on)}$	$V_{DD}=300V, I_D=12A,$ $R_G=25\Omega$ (Note 2,3)	-	37	-	ns
Turn-On Rise Time	t_r		-	72	-	
Turn-Off Delay Time	$t_{d(off)}$		-	81	-	
Turn-Off Fall Time	t_f		-	44	-	
Drain-Source Diode						
Maximum Continuous Drain-Source Diode Forward Current	I_S	---	-	-	12	A
Maximum Pulsed Drain-Source Diode Forward Current	I_{SM}	---	-	-	48	A
Reverse Recovery Time	t_{rr}	$V_{GS}=0V, I_S=12A$	-	574	-	ns
Reverse Recovery Charge	Q_{rr}	$di_F/dt=100A/\mu s$ (Note 2)	-	5.4	-	μC

NOTES :

1. $L=30\text{mH}, I_{AS}=7.1A, V_{DD}=50V, R_G=25\text{ohm}$, Starting $T_J=25^\circ\text{C}$
2. Pulse width $\leq 300\mu s$, Duty cycle $\leq 2\%$
3. Essentially independent of operating temperature typical characteristics.
4. Guaranteed by design, not subject to production testing



PJP12NA60 / PJF12NA60

TYPICAL CHARACTERISTIC CURVES




Fig.1 Output Characteristics




Fig.2 Transfer Characteristics




Fig.3 On-Resistance vs. Drain Current




Fig.4 Source-Drain Diode Forward Voltage




Fig.5 Capacitance vs. Drain-Source Voltage




Fig.6 Gate Charge



PJP12NA60 / PJF12NA60

TYPICAL CHARACTERISTIC CURVES




Fig.7 BV_{DSS} vs. Junction Temperature




Fig.8 On-Resistance vs. Junction Temperature




Fig.9 Threshold Voltage Variation with Temperature




Fig.10 Maximum Safe Operating Area




Fig.11 Maximum Safe Operating Area



PJP12NA60 / PJF12NA60

TYPICAL CHARACTERISTIC CURVES




Fig.13 PJP12NA60 Normalized Transient Thermal Impedance vs. Pulse Width






Fig.14 PJF12NA60 Normalized Transient Thermal Impedance vs. Pulse Width



PJP12NA60 / PJF12NA60

Packaging Information





PJP12NA60 / PJF12NA60

PART NO PACKING CODE VERSION

Part No Packing Code	Package Type	Packing type	Marking	Version
PJP12NA60_T0_00001	TO-220AB	50pcs / Tube	P12NA60	Halogen free
PJF12NA60_T0_00001	ITO-220AB-F	50pcs / Tube	F12NA60	Halogen free



PJP12NA60 / PJF12NA60

Disclaimer

- Reproducing and modifying information of the document is prohibited without permission from Panjit International Inc..
- Panjit International Inc. reserves the rights to make changes of the content herein the document anytime without notification. Please refer to our website for the latest document.
- Panjit International Inc. disclaims any and all liability arising out of the application or use of any product including damages incidentally and consequentially occurred.
- Panjit International Inc. does not assume any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.
- Applications shown on the herein document are examples of standard use and operation. Customers are responsible in comprehending the suitable use in particular applications. Panjit International Inc. makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.
- The products shown herein are not designed and authorized for equipments requiring high level of reliability or relating to human life and for any applications concerning life-saving or life-sustaining, such as medical instruments, transportation equipment, aerospace machinery et cetera. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Panjit International Inc. for any damages resulting from such improper use or sale.
- Since Panjit uses lot number as the tracking base, please provide the lot number for tracking when complaining.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panjit:

[PJF12NA60_T0_00001](#)