


PART NO. AND CH. CODE	$\Delta W_{\pm 0.4}$	H ₁	$\Delta W_{\pm 0.4}$	H ₂	X	Y	Z	WIRE SIZE	MATERIAL
7116-6045	3.60	$\Delta(3.34)$	5.80	$\Delta(4.93)$	0	0	0	AVS 0.5~AVS 1.25 EQUIVALENT	Δ C2600 (t=0.40) TIN PLATING
7116-6046	4.90	$\Delta(4.62)$	7.40	$\Delta(6.10)$	0	0	0	AVS 2~AVS 3 EQUIVALENT	Δ C2600 (t=0.40) TIN PLATING
7116-6047	6.80	$\Delta(6.48)$	9.90	$\Delta(8.29)$	1.10	4.00	5.50	AVS 5~AV 8 EQUIVALENT	Δ COPPER ALLOY (t=0.40) TIN PLATING

- 注記
 1. 嵌合相手品番: 7114-6045 ETC.
 2. 通用工機品番: 7158-3022-80 ETC.

- NOTES
 1. MATING PART NO.: 7114-6045 ETC.
 2. APPLICABLE RUBBER STOPPER NO.: 7158-3022-80 ETC.



REV. NO.	DATE	CHANGED MATERIAL & DIMENSION	NEW	REVISION RECORD	CUSTOMER	CUSTOMER PART NO.	CUSTOMER DWG NO.	TRIAL PART NO.	NAME
00.01.28		CHANGED MATERIAL		C00-L150	C.I.T				
98.08.04		CHANGED NOTES & DIMENSION		C97-N466	H.K				
90.03.06		CHANGED FORM		C90-L254	K.O				
89.10.11		NEW		C89-M090	H.Y				
LET	DATE	REVISION RECORD		NO.	CHKD				
GENERAL TOLERANCE									
10MAX	50MAX	100MAX	250MAX	250OVR	ANGLE	ECCENT			
A ± 0.15	± 0.2	± 0.3	± 0.5	± 0.75	$\pm 30'$	0.1			
B ± 0.2	± 0.3	± 0.55	± 0.95	± 1.4	$\pm 30'$	0.1			
C ± 0.3	± 0.5	± 0.8	± 1.4	± 2	$\pm 30'$	0.15			
SPECIFIED									
MASS									
g									
DWG TYPE									
NEW									
CHECKED									
DESIGN									
DRAWN									
APPROVED									
R									
DWG DATE									
89.10.19									
UNIT									
mm									
SCL									
2/1									
ANGLE									
3									
PART NO.									
7116-6045 ETC.									
CH. CODE									
7116-6045:R									
SET DWG NO.									
YAZAKI CORPORATION									

1 2 3

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Yazaki:](#)

[71166045](#) [71166046](#) [71166047](#)