







7287-8879-30
KEYWAY A LEFT




7287-8886-90
KEYWAY D RIGHT




EXPLODED VIEW
(1/1)




7287-8880-30
KEYWAY A RIGHT




7287-8881-40
KEYWAY B LEFT




7287-8882-40
KEYWAY B RIGHT




7287-8883-60
KEYWAY C LEFT




7287-8884-60
KEYWAY C RIGHT




7287-8885-90
KEYWAY D LEFT




MINIMUM PASS-THROUGH HOLE DIMENSION WITH LEVER IN PRE-SET
(1mm CLEARANCE ALL AROUND)
(1/1)



FRONT ISOMETRIC VIEW
(LEVER IN PRE-SET POSITION)
(1/1)






FRONT ISOMETRIC VIEW
(SHIPPING POSITION)
(1/1)




REAR ISOMETRIC VIEW
(1/1)

TABLE 1	SUB-ASSEMBLY PART NUMBER	NO.	PART NUMBER	PART NAME	MATERIAL	COLOR	QUANTITY
	SEE TABLE 2	①	SEE TABLE 2	42P (26Px1.5mm + 12Px2.8mm + 4Px6.3mm) LIF YESC KAIZEN UNSEALED FEMALE HOUSING	PBT-GF15	SEE TABLE 2	1
		②	7172-0672	42P (26Px1.5mm + 12Px2.8mm + 4Px6.3mm) LIF YESC KAIZEN UNSEALED FEMALE FRONT HOLDER	PBT	NATURAL	1
		③	7173-2055	42P (26Px1.5mm + 12Px2.8mm + 4Px6.3mm) LIF YESC KAIZEN UNSEALED FEMALE LEVER	PBT-GF15	NATURAL	1
TABLE 2			SUB ASSEMBLY PART NUMBER	HOUSING PART NUMBER	KEYWAY	COLOR	
			7287-8879-30	7187-8879-30	A	BLACK	
			7287-8880-30	7187-8879-30	A	BLACK	
			7287-8881-40	7187-8881-40	B	LIGHT GRAY	
			7287-8882-40	7187-8881-40	B	LIGHT GRAY	
			7287-8883-60	7187-8883-60	C	GREEN	
			7287-8884-60	7187-8884-60	C	GREEN	
			7287-8885-90	7187-8885-90	D	BLUE	
			7287-8886-90	7187-8885-90	D	BLUE	



SECTION A-A



- NOTES:
- 1. PARTS MUST BE PURCHASED FROM YAZAKI.
 - 2. PARTS MUST BE FREE OF FLASH AND IMPERFECTIONS THAT AFFECT FUNCTION.
 - 3. APPLICABLE TERMINAL: 1176-4780-02 R DRAWING (YES KAZEEN 1 UNSEALED)
MAX WIRE OD: 2.0mm (CAVITIES 4, 6, 8, 18, 25, 27-37, 39)
SEE 1176-4270-02 R DRAWING (YES KAZEEN 2 UNSEALED)
MAX WIRE OD: 3.0mm (CAVITIES 2, 3, 5, 17, 19, 20, 23, 24, 26, 38, 40, 41)
 - 4. APPLICABLE TERMINAL: 1176-4120-02 R DRAWING (YES KAZEEN 3 UNSEALED)
MAX WIRE OD: 4.30mm (CAVITIES 1, 21, 22, 42)
 - 5. MATING PART NUMBER: 7287-8879-30 DRAWING
 - 6. PART SATISFIES USCAR 2, REVISION 5, NOVEMBER 2007, (TZV12/S1/MF3)
 - 7. PART TO COMPLY WITH YPS-31-038 REQUIREMENTS.
 - 8. THIS DIMENSION SHOWS THE PRE-SET POSITION OF THE TPA.
 - 9. THIS DRAWING IS TO BE USED FOR INTERNAL YAZAKI PSW SUBMISSION.
 - 9. HANDLING MANUAL: YPS-15-1553E
 - 10. APPLICABLE FIRE COVER PART NUMBER: 7174-1436
 - 11. FOR CONNECTOR CPA CAPABILITY PLEASE REFER TO 7286-7510-30, ETC.

CUSTOMER		CUSTOMER PART NO.		CUSTOMER DWG NO.		MATERIAL SPEC.		SEE TABLE		TREAT. & FIN.		ISSUE MARK	
OFFICE		YNA		TRIAL PART NO.		NAME		42P (26Px1.5mm + 12Px2.8mm + 4Px6.3mm) LIF					
VENDOR								YESC KAIZEN UNSEALED (F) SUB-ASSEMBLY					
VENDOR NO.													
DWG TYPE		DWG SOURCE		DWG DATE		UNIT		SCL		ANGLE		PART NO.	
R		7287-8879-30		09-22-2016		mm		2/1		3		CH. CODE	
APPROVED		CHECKED		DESIGN		DRAWN						7287-8879-30.	
												DWG NO.	
				JEN YUN NG		KAREN MARQUEZ						7287-8879-30:R	
				10-19-2011		09-28-2021						YAZAKI CORPORATION	

GENERAL TOLERANCE											
	10MAX	50MAX	100MAX	250MAX	2500VR	R5 MAX	R10 MAX	R20 MAX	R20 OVR	ANGLE	ECCENT
A	±0.15	±0.20	±0.30	±0.50	±0.75	±0.2	±0.3	±0.5	±2.5	±3°	0.1
B	±0.20	±0.30	±0.55	±0.95	±1.40					±3°	0.1
(C)	±0.30	±0.50	±0.80	±1.40	±2.00					±3°	0.15
SPECIFIED										MASS	 (54.47) g

⚠	09-08-2021	REVISED FORM, TERMINAL WIRE CAPABILITY AND MASS	C21-A673	KM
-	09-22-2016	NEW	C16-A666	HA
LET	DATE	REVISION RECORD	NO.	CHKD

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Yazaki:](#)

[7287888030](#) [7287888140](#) [7287888460](#) [7287887930](#) [7287888690](#) [7287888240](#) [7287888360](#) [7287888590](#)