



REV	ECN NO	REVISIONS	DRN	CKD	APP	QA	CM	DATE
A	127925	NEW RELEASE	LD	CS				2-26-25



LED SCHEMATIC



- 1. GREEN ANODE
- 2. COMMON CATHODE
- 3. RED ANODE

NOTES:

1. DIALIGHT PART NO: 521-8739F
2. THIS ASSEMBLY CONTAINS ELECTROSTATIC DISCHARGE SENSITIVE DEVICES (ESDS). MAINTAIN ALL PRECAUTIONARY MEASURES DURING ASSEMBLY, HANDLING AND STORAGE IN ACCORDANCE WITH IPC-A-610.
3. THIS PRODUCT IS RoHS COMPLIANT. EACH BAG MUST BE MARKED WITH RoHS COMPLIANT LABEL OR EQUIVALENT MARKINGS. LED MUST BE Pb FREE (RoHS COMPLIANT).

OPERATING CHARACTERISTICS AT 25°C AMBIENT										
LED COLOR	DOMINANT WAVELENGTH (nm)			LUMINOUS INTENSITY (mcd) @ I <sub>F</sub> =20mA			FORWARD VOLTAGE (V) @ I <sub>F</sub> =20mA			VIEWING ANGLE (DEG)
	MIN	TYP	MAX	MIN	TYP	MAX	MIN	TYP	MAX	TYP
RED		630		1100		1800	1.5		2.4	40
GREEN		574		450		470	1.7		2.6	40

ABSOLUTE MAXIMUM RATINGS AT 25°C AMBIENT			
	RED	GREEN	UNITS
POWER DISSIPATION	75	75	mW
PEAK FORWARD CURRENT (1/10 DUTY CYCLE, 10ms PULSE WIDTH)	90	60	mA
CONTINUOUS FORWARD CURRENT	30	30	mA
LEAD SOLDERING TEMPERATURE (.079" [2mm] FROM BODY) FOR 5 SEC.	260		°C
OPERATING TEMPERATURE	-40 TO +85		°C
STORAGE TEMPERATURE	-40 TO +100		°C

THIS DRAWING AND THE CONTENTS HEREIN ARE CONFIDENTIAL AND THE SOLE PROPERTY OF DIALIGHT CORP. REPRODUCTION OF THIS DRAWING OR CONSTRUCTION OF ANY PARTS WITHIN THIS DRAWING ARE FORBIDDEN WITHOUT THE WRITTEN CONSENT OF DIALIGHT CORP.

SCALE: 5.000	DRAWING NUMBER	REV
ALL DIM'S: INCH (mm)	C-18803	A
TOLERANCES: UNLESS OTHERWISE SPECIFIED	TITLE	
FRACTIONS: ±1/64	R/G 5mm WATER CLEAR LED	
DECIMALS (.XX): ±.01	MATERIAL	
DECIMALS (.XXX): ±.010	Dialight	
ANGLES: ±1°	1501 ROUTE 34 SOUTH	
FINISH	FARMINGDALE, NJ 07727	
	(732) 919-3119	
	www.dialight.com	
FSCM 83330	SHEET 1 OF 1	FAMILY TABLE:

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Dialight:](#)

[521-8739F](#)