





TOLERANCE UNLESS OTHERWISE SPECIFIED	
.X	±0.15
.XX	±0.10

THIS IS A C.A.D. GENERATED DRAWING
DO NOT MAKE MANUAL REVISIONS TO MASTER.



ISSUE NUMBER	1
ORIGINAL	



RECOMMENDED PCB LAYOUT (T:1.2mm)
TOLERANCE UNSPECIFIED ±0.05mm

SPECIFICATION:
MATERIAL:

CONTACT: BRASS GOLD FLASH PLATING ALL OVER NICKEL UNDERPLATING
MAGNET: N52
HOUSING: PA9T, BLACK

ELECTRICAL:

RATED VOLTAGE (PER CONTACT): 5V
RATED CURRENT (PER CONTACT): 2A
INSULATION RESISTANCE: 100MEGAOHMS MINIMUM
DIELECTRIC WITHSTANDING VOLTAGE: 100V AT 60Hz
CONTACT RESISTANCE: 30mOHMS MAXIMUM BEFORE TEST AND 60mOHMS MAXIMUM

MAGNETIC SPRING LOADED CONNECTOR,
3POS, FEMALE

ACAD REFERENCE NO.:	686F0321350120E	UNIT: MM
DRAWN:	J.L.	DATE: 2023-05-05
CHECKED:	R.S.M	DATE: 2023-05-05
SCALE:	(IN CAD 1:1)	SHEET 1 OF 1
DRAWING NUMBER:	686F0321350120E	ISSUE
PART NUMBER:	686F0321350120E	1



THIS SERIES FULLY CONFORMS TO
THE EUROPEAN UNION DIRECTIVES
2011/65/EU FOR RoHS COMPLIANCY.



YOUR CONNECTION TO QUALITY & SERVICE

EDAC INC
TORONTO, ONTARIO
CANADA

THESE DRAWINGS AND SPECIFICATIONS
ARE THE PROPERTY OF EDAC INC., AND
SHALL NOT BE REPRODUCED, OR COPIED
OR USED AS THE BASIS FOR THE
MANUFACTURE OR SALE OF APPARATUS
WITHOUT WRITTEN PERMISSION.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[EDAC:](#)

[686F0321350120E](#)