




CIRCUIT: DPDT

SWITCH FUNCTION		
POS. 1	POS. 2	POS. 3
		
(DN)	OFF	(DN)
2-3,5-6	OPEN	2-1,5-4

## NOTES:


1. ALL DIMENSIONS IN MM  
2. GENERAL TOLERANCE: X.X=±0.4  
X.XX=±0.25

$$X.XX = \pm 0.25$$

3. TERM. NOS. FOR REF. ONLY  
4. RATING: 0.4VA @20 max. (AC or DC)  
5. MATERIAL: FIXED TERMINAL & MOVING CONTACT  
Copper Alloy w/Gold plate over  
Nickel plate. ▲

Copper Alloy w/Gold plate over Nickel plate.

6. CONTACT RESISTANCE: 10mILLI Ohms max initial @2-4VDC, 100mA for AG & AU
7. ELECTRICAL LIFE: 50,000 make-and-break cycles at full load.
8. INSULATION RESISTANCE: 1,000M Ohm min.
9. DIELECTRIC STRENGTH: 1000V RMS @sea level
10. OPERATING TEMP.: -30°C to 85°C



## RECOMMENDED PANEL MOUNTING

E-SWITCH®

			TITLE			
			300 DP-4 J3 VSE R E (GOLD CONTACTS)			
A	12759	RELEASED FOR PRODUCTION	1/27/03	CB		
REV.	ECN NO.	DESCRIPTION	DATE	CHKD		
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED						
SCALE			1.5:1	DATE	1/27/03	DR
					CB	DWG
					T324014	REV
						A

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[300DP4J3BLKVS2RE](#)