



NOTES:

1. ALL DIMENSIONS IN MM[INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. TERM. NOS. FOR REFERENCE ONLY.
4. RATING: 4A @ 125VAC, 2A @ 250VAC
5. CONTACT RESISTANCE: 10 milli-OHMS MAX.
6. DIELECTRIC STRENGTH: 1,500 VAC-1Minute
7. MATERIALS:
HOUSING: NICKEL PLATED ZINC ALLOY
CYLINDER: NICKEL PLATED ZINC ALLOY
TERMINAL AND CONTACTS: GOLD PLATED COPPER ALLOY
KEYS (2): BRASS
8. ONE HEX MOUNTING NUT SUPPLIED PER SWITCH
9. 2002/95/EC (ROHS) COMPLIANT
10. ▲ DENOTES CRITICAL PARAMETER



SWITCH FUNCTION	
CONNECTED TERMINAL #	
POS. A	POS. B
8 - 1	1 - 3

- LEGEND
- = Detent positions
 - ⊙ = Key pull possible in these positions



TITLE KO130N602

A	18646	Released For Production	10/1/09	BLR
REV	PCR NO	DESCRIPTION	DATE	BY

SCALE	DATE	DR	DWG	REV
1:1	10/1/2009	BLR	K200297	A

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[KO130N602](#)