



- NOTES:
1. ALL DIMENSIONS IN MM [INCH]
  2. GENERAL TOLERANCE: X.X = ±0.4  
X.XX = ±0.25
  3. RATING: 20VDC @ 1mA, 5VDC @ 5mA
  4. CONTACT RESISTANCE: 200Ω MAX.
  5. INSULATION RESISTANCE: 100MΩ MIN. @ 100VDC.
  - ▲ 6. OPERATING FORCE: 125 ± 35gf
  7. TRAVEL: 1.25 ± 0.3 mm
  8. OPERATING TEMPERATURE: -40°C to 85°C
  9. OPERATING LIFE: 1,000,000 CYCLES
  - ▲ 10. LED: WHITE
  11. ▲ DENOTES CRITICAL PARAMETERS
  12. CONTACT MATR'L: GOLD FLASH OVER NICKEL



▲ WHITE CAP  
with  
WHITE LED



▲ LED SPECS		UNITS	WHITE	
FORWARD CURRENT		mA	20	
FORWARD VOLTAGE @ 20mA		VDC	3.3 TYP	4.0 MAX.
LUMINOUS INTENSITY @ 20mA		mcd	400 TYP.	

REV	ECO NO	DESCRIPTION	DATE	BY
B	ECO-101243	UPDATE TO CURRENT LED SPECS	09/22/22	JS

		OBJECT ID 000006818
TITLE LP15R1WHTWHT-N		

SCALE 2:1	DATE 9/11/2017	DR MW	DWG B270010	REV B
--------------	-------------------	----------	----------------	----------

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[LP15R1WHTWHT-N](#)