


P.C.B. LAYOUT



SWITCH FUNCTION			
POS. 1	POS. 2	POS. 3	
			ON
2-3,5-6	OPEN	2-1,5-4	




CIRCUIT: DPDT

NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: ± 0.4
3. TERMINAL NUMBERS FOR REF ONLY
4. PLATING MATERIAL: SILVER
5. RATING: 5 AMPS @ 120VAC OR 28VDC
2 AMPS @ 250VAC
6. ELECTRIC LIFE: 40,000 make-and-break cycles at full load.
7. INSULATION RESISTANCE: 1,000 Mega-ohm min.
8. DIELECTRIC STRENGTH: 1,000 V RMS @sea level.
9. OPERATING TEMP.: -30°C to 85°C
10. HARDWARE TO BE SHIPPED BULK
 - T100000 - HEXNUT - QTY 2
 - T100011 - LOCKWASHER - QTY 1
 - T100002 - LOCKRING - QTY 1
 - T100016 - O-RING - QTY 1
11. ▲ DENOTES CRITICAL PARAMETER.



ISOMETRIC



E-SWITCH®				
TITLE 100DP3T1B9M2QEH				
SCALE 2:1		DATE 6/1/2005	DR JB	DWG ST106003
REV		REV C		

C	19539	UPDATE DRAWING	12/21/10	BGL
B	15063	CORRECTED NOTE #10	7/11/05	JB
A	14968	RELEASED FOR PRODUCTION	6/1/05	JB
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[100DP3T1B9M2QEH](#)