




O.P. (MM)	P.T. (MM)
14.75±0.5	.9 NOM

O.P. = OPERATING POINT  
P.T. = PRE-TRAVEL



- NOTES:
1. ALL DIMENSIONS IN MM [INCH]
  2. GENERAL TOLERANCE: X.X±0.4  
X.XX±0.25
  3. RATING: 0.4VA @20VAC OR DC
  - ▲ 4. OPERATING FORCE: 160 ± 40 GRAMS
  5. OPERATING TEMP: -25°C TO 85°C
  6. ELECTRICAL LIFE: 50,000 CYCLES.
  7. MECHANICAL LIFE: 1,000,000 CYCLES.
  8. INSULATION RESISTANCE: >100 MEGA-OHMS @ 500VDC
  9. DIELECTRIC STRENGTH: 1500VAC 1 MINUTE (INITIAL VALUE)
  10. CONTACT RESISTANCE: 100 MILLI -OHMS MAX.
  11. ▲ DENOTES CRITICAL PARAMETER.
  - ▲ 12. CONTACTS: 10 MICRO INCHES MINIMUM GOLD PLATING (P/N Q990000)
  13. 2002/95/EC (ROHS) COMPLIANT

**E-SWITCH®**

TITLE LS085R100F160C2A

A	21147	RELEASED FOR PRODUCTION	6/4/13	EBP
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

SCALE	DATE	DR	DWG	REV
	6/4/2013	EBP	Q950108	A

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[LS085R100F160C2A](#)