






RECOMMENDED PANEL CUTOUT  
MAX. PANEL THICKNESS 0.7~2.5mm

SWITCH FUNCTION	
POS. 1	POS. 2
OPEN	1-3, 2-4



## NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X =  $\pm 0.5$   
X.XX =  $\pm 0.30$
3. TERMINAL NUMBERS FOR REF. ONLY
- ▲ 4. RATING: 16(16)A @ 127VAC
5. CONTACT RESISTANCE: 50mΩ MAX.
6. INSULATION RESISTANCE: 2MΩ @ 500VDC
7. DIELECTRIC STRENGTH: 1,300VAC MIN. FOR 1 MINUTE
8. ELECTRICAL LIFE: 50,000 CYCLES
9. OPERATING TEMPERATURE: 0°C to 55°C
10. ACTUATION FORCE: 13  $\pm$  5N (AT 5mm TRAVEL)
11. INGRESS PROTECTION: IP66 (AFTER MOUNTING)
12. ▲ DENOTES CRITICAL PARAMETER
13. 2011/65/EU (ROHS) COMPLIANT



REV	ECO NO	DESCRIPTION	DATE	BY	E-SWITCH®				OBJECT ID
B	ECO-101925	PRINT UPDATE	05/30/23	JS					100123380
A	ECO-101536	NEW RELEASE	01/12/23	MR	TITLE PB66EE2CR6N				
					SCALE 1:1	DATE 12/27/2022	DR MJR	DWG 34-PB66EE2CR6N	REV B

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO  
E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[PB66EE2CR6N](#)