



CIRCUIT: SPDT
CONTACT CONFIGURATION

SWITCH FUNCTION		
POS. 1	POS. 2	POS. 3
<DN>	OFF	<DN>
2-3	OPEN	2-1

()=Momentary



RECOMMENDED P.C.B. LAYOUT



NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: 0.0=±0.4
0.00=±0.25
3. TERM. NOS. FOR REF. ONLY
4. RATING: .4VA max. @ 20VDC OR VAC max.
5. FIXED TERM. MOVING CONTACT: GOLD OVER NICKEL OVER COPPER ALLOY
6. ELECTRICAL LIFE: 30,000 make-and-break cycle at full load.
7. DIELECTRIC STRENGTH: 1,000 V RMS @sed level.
8. OPERATING TEMP.: -30°C to 85°C

TITLE				200 MSP-4 T2 B4 M7 R E			
SCALE				2:1			
DATE				1/24/02			
DR				CJC			
DWG				T211085			
REV				A			
REV.				A			
ECN No.				11945			
DESCRIPTION				RELEASED FOR PRODUCTION			
DATE				1/24/02			
CHKD				CJC			
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED							

E-SWITCH®

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[200MSP4T2B4M7RE](#)