




| SWITCH FUNCTION | |
|---|---|
| POS. 1 | POS. 2 |
|  |  |
| OFF | (ON) |
| OPEN | 1-2 |

(ON) = MOMENTARY



Ø16.00
[.630 in]



PANEL CUTOUT
MAX. PANEL THICKNESS 6.0mm

Ø18.00
[.709 in]

Ø12.00
[.472 in]



CIRCUIT: SPST

▲ BODY FINISH
POLISHED FINISH
STAINLESS STEEL

▲ FLAT ACTUATOR
POLISHED FINISH
STAINLESS STEEL

1.50 ± .50
[.059 ± .020 in]

14.00 ± .50
[.551 ± .020 in]

17.00 ± .50
[.669 ± .020 in]

.50
[.020 in]

8.50
[.335 in]

2.00
[.079 in]

.80
[.031 in]

M16x1.0

NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERMINAL NUMBERS FOR REF ONLY
4. CONTACT MATERIAL: SILVER
5. RATING: 2A 48VDC
- ▲ 6. TRAVEL: 1.5 ± 0.2mm
7. ELECTRIC LIFE: 200,000 MAKE-AND-BREAK CYCLES
8. INSULATION RESISTANCE: 1,000 MΩ MIN.
9. DIELECTRIC STRENGTH: 2,000 VAC MIN. FOR 1 MINUTE
10. CONTACT RESISTANCE: 50mΩ MAX. @ 1A 12VDC
11. OPERATING TEMP.: -20°C to 55°C
12. ▲ DENOTES CRITICAL PARAMETER.
13. INGRESS PROTECTION: IP65
- ▲ 14. HARDWARE SUPPLIED: O-RING AND HEXNUT
15. 2002/95/EC (ROHS) COMPLIANT



TITLE PV2F240SS

| | | | | |
|-----|--------|---------------------|----------|-----|
| C | 20337 | REVISED AND REDRAWN | 12/13/11 | BGL |
| REV | PCR NO | DESCRIPTION | DATE | BY |

| | | | | |
|-------|------------|-----|--------------|-----|
| SCALE | DATE | DR | DWG | REV |
| 2:1 | 12/13/2011 | BGL | 52-PV2F240SS | C |

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[PV2F240SS](#)