





SWITCH	WIRE	LENGTH
SW1-1	WIRE, 22AWG AWM UL1007, YELLOW	300.0 [11.8 in]
SW1-2	WIRE, 22AWG AWM UL1007, BLUE	300.0 [11.8 in]
SW1-3	WIRE, 22AWG AWM UL1007, GREEN	300.0 [11.8 in]
SW1-4	WIRE, 22AWG AWM UL1007, PURPLE	300.0 [11.8 in]
SW1-5	WIRE, 22AWG AWM UL1007, ORANGE	300.0 [11.8 in]
SW1-6	WIRE, 22AWG AWM UL1007, WHITE	300.0 [11.8 in]
SW1- (+)	WIRE, 22AWG AWM UL1007, RED	300.0 [11.8 in]
SW1- (-)	WIRE, 22AWG AWM UL1007, BLACK	300.0 [11.8 in]



RECOMMENDED PANEL CUTOUT  
MAX. PANEL THICKNESS 8.0 [.31 in]

NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X =  $\pm 0.4$   
X.XX =  $\pm 0.25$
3. TERMINAL NUMBERS FOR REF ONLY
- ▲ 4. CONTACT MATERIAL: GOLD
5. RATING: 2A 48VDC
- ▲ 6. LAMP VOLTAGE: 6V
7. INGRESS RATING: IP67
8. ELECTRIC LIFE: 50,000 MAKE-AND-BREAK CYCLES AT FULL LOAD.
9. INSULATION RESISTANCE: 1,000 M $\Omega$  MIN.
10. DIELECTRIC STRENGTH: 2,000 VAC MIN. FOR 1 MINUTE
11. CONTACT RESISTANCE: 50m $\Omega$  MAX. @ 1A 12VDC
12. OPERATING TEMP.: -20°C to 55°C
13. ▲ DENOTES CRITICAL PARAMETER.
14. SUPPLIED HARDWARE: O-RING AND HEXNUT
- ▲ 15. USE PART NUMBERS DESIGNATED OR ENGINEERING APPROVED EQUIVALENTS.



SWITCH  
BODY - BLACK ANODIZED  
ACTUATOR - BLACK ANODIZED  
RING ILLUMINATION - RED

REV	ECO NO	DESCRIPTION	DATE	BY	E-SWITCH®			OBJECT ID	
A	ECO-102495	RELEASE	01/25/24	JS				100126662	
					TITLE PV3WFWH011G-313				
					SCALE 2:3	DATE 1/22/2024	DR JS	DWG 52-PV3WFWH011G313	REV A

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[PV3FWH011G-313](#)