





▲ SWITCH FUNCTION




POS. 1	POS. 2
1-2	(3-4)

() = MOMENTARY



NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. TERMINAL NUMBERS FOR REF. ONLY
4. RATING: 2A @ 48VDC
5. CONTACT RESISTANCE: 50m Ω MAX. @ 1A 12VDC
6. INSULATION RESISTANCE: 1,000M Ω @ 500VDC
7. DIELECTRIC STRENGTH: 2,000VAC MIN. FOR 1 MINUTE
8. ELECTRICAL LIFE: 50,000 CYCLES
9. OPERATING TEMPERATURE: -20°C TO 55°C
10. INGRESS PROTECTION: IP66
11. ▲ DENOTES CRITICAL PARAMETER
12. SUPPLIED HARDWARE: O-RING AND HEXNUT
13. ILLUMINATION COLOR: GREEN
14. ILLUMINATION VOLTAGE: BASE VOLTAGE 2.8 V



D	24637	UPDATE THREAD LENGTH TO 15.0	12/10/20	JM
C	23839	UPDATED RATING TO IP66	4/8/19	MJR
B	22589	Update to correct Housing	11/10/16	MW
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED



TITLE PV9F2V0SS-331

SCALE 1:1

DATE 7/16/2014

DR RC

DWG 52-PV9F2V0SS331

REV D

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[PV9F2V0SS-331](#)