









NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: $X.X = \pm 0.4$
 $X.XX = \pm 0.25$
3. TERM. NOS. FOR REFERENCE ONLY.
4. RATING: 12VDC, 100mA
5. CONTACT MATERIAL: GOLD PLATED
6. CONTACT RESISTANCE: 200 mΩ MAX.
7. INSULATION RESISTANCE: 500VDC, 100 MΩ MIN.
8. OPERATING FORCE: $200 \pm 100\text{gf}$
9. MECHANICAL LIFE: 2,000,000 CYCLES
10. OPERATING TEMP: -40°C to +85°C
- ▲ 11. LED COLORS: RED/RED, 1.6-2.5V @ 20mA
12. TRAVEL: 4.00mm ± 0.20
13. ▲ DENOTES CRITICAL PARAMETER.
- ▲ 14. SWITCH HAS NON TACTILE FEEDBACK WHEN ACTUATED



B	24664	correct O.F. and remove E	1/6/21	MW
A	24634	RELEASE	12/11/20	MW
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED



E-SWITCH®

TITLE	LP11EE1NBSRR
-------	--------------

SCALE 3:2

DATE 12/9/2020

DR	MW
----	----

DWG
B232008

REV
B

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[LP11EE1NBSRR](#)