






▲	O.P. (MM)	P.T. (MM)
	8.5 ±0.3	1.1 MAX

O.P. = OPERATING POINT
P.T. = PRE-TRAVEL



CIRCUIT: SPDT



NOTES:

- | | |
|--|--------|
| 1. ALL DIMENSIONS IN MM [INCH] | 1.8 |
| 2. GENERAL TOLERANCE: X.X=±0.4 | [.075] |
| X.XX=±0.25 | |
| 3. RATING: 0.4VA @20V (AC OR DC) | 8 |
| ▲ 4. OPERATING FORCE: 130 ± 40 GRAMS | [.34] |
| 5. OPERATING TEMP: -25°C TO 85°C | |
| 6. ELECTRICAL LIFE: 50,000 CYCLES MIN. | 5 |
| 7. MECHANICAL LIFE: 1,000,000 CYCLES TYP. | [.20] |
| 8. INSULATION RESISTANCE: 100 MΩ MIN. | |
| 9. DIELECTRIC STRENGTH: 1000VAC 1 MINUTE (INITIAL VALUE) | |
| 10. CONTACT RESISTANCE: 100 mΩ MAX. | |
| ▲ 11. CONTACTS: 10 MICRO INCHES MINIMUM GOLD PLATING (PN: Q990001) | |
| 12. ▲ DENOTES CRITICAL PARAMETER. | |
| 13. 2002/95/EC (ROHS) COMPLIANT | |



A	20162	RELEASED FOR PRODUCTION	9/22/11	BGL
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

				
TITLE MS085R100F130C1A				
SCALE 2:1	DATE 9/22/2011	DR BGL	DWG Q970120	REV A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[MS085R100F130C1A](#)