




1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X $\pm$ 0.4
X.XX $\pm$ 0.25
3. TERMINAL NUMBERS FOR REF. ONLY
4. CONTACT RATING: 0.1A @ 30VDC
5. CONTACT RESISTANCE: 50m OHM MAX
6. TRAVEL: FULL = 2.5 $\pm$ 0.3; LOCK = 1.5 $\pm$ 0.3mm'S
7. OPERATING FORCE: 250 $\pm$ 100gf
8. ELECTRICAL LIFE: 10,000 CYCLES
9. ▲DENOTES CRITICAL PARAMETER
10. CONTACT MATERIAL: SILVER
11. OPERATING TEMPERATURE: -20c TO +70c
12. INSULATION RESISTANCE: 100M OHMS MIN.
13. LED COLOR: BLUE
14. 2002/95/EC (RoHS) COMPLIANT AND HALOGEN FREE



7. OPERATING FORCE: 250±100gJ
8. ELECTRICAL LIFE: 10,000 CYCLES
9. ▲ DENOTES CRITICAL PARAMETER
10. CONTACT MATERIAL: SILVER
11. OPERATING TEMPERATURE: -20c TO +70c
12. INSULATION RESISTANCE: 100M OHMS MIN.
▲ 13. LED COLOR: BLUE



B	15534	DIM CHANGES & UPDATES		12/30/10	BGL
A	18806	New-Release		1/20/10	rc
REV	PCR NO	DESCRIPTION	DATE	BY	
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED					
SCALE		2	DATE	1/20/2010	DR rc
					DWG B401002
					REV B
TITLE		TL2205EEBPBA			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[TL2205EEBPBA](#)