









NOTES:

1. ALL DIMENSIONS IN MM
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. TERM. NOS. FOR REFERENCE ONLY.
4. CONTACT RATING: 0.5A @ 100 VAC OR 25 VDC
- ▲ 5. CONTACT MATERIAL: SILVER
6. ELECTRICAL LIFE: 200,000 TYP.
7. MECHANICAL LIFE: 200,000 CYCLES TYP.
8. OPERATING TEMP: -40°C to +85°C
9. OPERATING FORCE: 200 $\pm$ 100 gf
10. CONTACT RESISTANCE: 50 MILLI-OHM INITIAL TYP. MAX.
11. INSULATION RESISTANCE: 500VDC, 100 M Ω MIN.
12. DIELECTRIC STRENGTH: 1000 VAC FOR 1 MINUTE
13. TRAVEL TO MAKE: 2.20mm $\pm$ 0.2
14. 2011/65/EU (ROHS) COMPLIANT
15. ▲ DENOTES CRITICAL PARAMETER
- ▲ 16. LED COLOR: GRN: 3 CHIPS; 2.1VDC, @20mA TYP.
BLU: 3 CHIPS; 3.3VDC, @20mA TYP.



A	22903	RELEASE	6/20/17	MW	TITLE ULP12EEP1QLSCL1GRNBLU				
REV	PCR NO	DESCRIPTION	DATE	BY					
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED					SCALE 2:1	DATE 6/15/2017	DR MW	DWG B800079	REV A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[ULP12EEP1QLSCL1GRNBLU](#)