


 $17.60^{+.20}_{-.00}$
 $[\text{.69}^{+.008}_{-.000} \text{ in}]$


PANEL CUT-OUT
PANEL THICKNESS 1-10mm

 $\phi 19.00^{+.20}_{-.00}$
 $[\phi .748^{+.008}_{-.000} \text{ in}]$
 $\phi 15.50$
 $[\text{.61 in}]$

 $\phi 22.00$
 $[\text{.87 in}]$

▲ POWER SYMBOL
ILLUMINATION
COLOR: BLUE



▲ ACTUATOR
BLACK ANODIZED



▲ HOUSING
BLACK ANODIZED


 2.0
 $[\text{.08 in}]$
 17.50 FLATS
 $[\text{.69 in}]$

M19 x 1.0
THREAD


 $.50$
 $[\text{.02 in}]$
 2.75
 $[\text{.11 in}]$
 13.00
 $[\text{.51 in}]$
 33.3
 $[\text{1.31 in}]$
 12.6
 $[\text{.49 in}]$
 32.7
 $[\text{1.29 in}]$

 17.5
 $[\text{.69 in}]$
 25.5
 $[\text{1.0 in}]$
 5.00
 $[\text{.197 in}]$
 2.80
 $[\text{.110 in}]$
 10.00
 $[\text{.394 in}]$

NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. TERMINAL NUMBERS FOR REF ONLY
- ▲ 4. CONTACT MATERIAL: SILVER
5. RATING: 3A 250 VAC cUL
6. ELECTRIC LIFE: 50,000 MAKE-AND-BREAK CYCLES
AT FULL LOAD
7. MECHANICAL LIFE: 1,000,000 CYCLES
8. INSULATION RESISTANCE: 1,000 M Ω @ 500VDC MIN.
9. DIELECTRIC STRENGTH: 2,000 VAC MIN. FOR 1 MINUTE
10. CONTACT RESISTANCE: 50m Ω MAX. @ 1A 12VDC
11. OPERATING TEMP.: -20°C to 55°C
12. ▲ DENOTES CRITICAL PARAMETER
- ▲ 13. LAMP VOLTAGE: 20mA 6V
14. TRAVEL: 3.2mm
15. ACTUATION FORCE: 2.5 $\pm$ 1.0 N
16. MOUNTING NUT TORQUE: 5-14 Nm
17. INGRESS PROTECTION: IP67
18. HARDWARE SUPPLIED: O-RING AND HEXNUT



REV	ECO NO	DESCRIPTION	DATE	BY	E-SWITCH®				OBJECT ID
B	ECO-100351	UPDATE PANEL CUTOOUT	12/09/21	JS	TITLE ULV4F2B11543				000026109
					SCALE	DATE	DR	DWG	REV
					3:2	12/6/2017	MW	T940109	B

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO
E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[ULV4F2B11543](#)