








RECOMMENDED P.C.B. LAYOUT



SWITCH FUNCTION	
PDS 1	PDS 2
ON	ON
2-1,5-4	2-3,5-6

NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERM. NOS. FOR REF. ONLY
4. RATING: 0.1A @30V DC
5. TRAVEL: 2.50±0.38
LOCK=1.34±0.38
6. OPERATING FORCE: 180±50gf
7. CONTACT RESISTANCE: 50mILLI-Ohms MAX. Initially
8. ELECTRICAL LIFE (at Full Load):
10,000 Cycles Make & Break
- ▲ 9. DESIGNATE MAJOR FEATURE:



TITLE TL2201EEZA1RBLK

SCALE 2:1

DATE 6/2/19

DR CB

DWG XP0203P

REV A

A	23920	RELEASED FOR PRODUCTION	6/5/19	MW
REV.	ECN No.	DESCRIPTION	DATE	CHKD

THE INFORMATION CONTAINED IN THIS DOCUMENT
IS PROPRIETARY TO E-SWITCH AND IS
NOT TO BE COPIED OR TRANSFERRED

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[TL2201EEZA1RBLK](#)