






## NOTES:

1. ALL DIMENSIONS IN mm [INCHES]
2. GENERAL TOLERANCE: x.x=  $\pm 0.4$   
x.xx=  $\pm .25$
3. TERM. NOS. FOR REF. ONLY
4. RATING: 0.1A; 30V
5. CONTACT RESISTANCE: 100 mILLI-OHMS MAX.
6. TIMING: NON-SHORTING
7. TRAVEL: FULL 1.8mm, LOCK 1.0mm
- ▲ 8. OPERATING FORCE:  $140 \pm 50\text{gf}$
9. ELECTRICAL LIFE: 10,000 CYCLES MAKE AND BREAK  
CYCLES AT FULL LOAD
10. ▲ DENOTE CRITICAL PARAMETER
11. 2002/95/EC (ROHS) COMPLIANT



TITLE TL2230EEF140

SCALE 3:1

DATE 12/12/2012

DR rc

DWG P010400

REV E

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY  
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

|     |        |                    |          |    |
|-----|--------|--------------------|----------|----|
| E   | 20929  | Updated PCB Layout | 12/17/12 | rc |
| REV | PCR NO | DESCRIPTION        | DATE     | BY |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[TL2230EEF140](#)