





ISOMETRIC



NOTES:

- 1. ALL DIMENSIONS IN MM
- 2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
- 3. TERM. NOS. FOR REFERENCE ONLY.
- ▲ 4. CONTACT RATING: 0.5A @ 100VAC
0.2A @ 250 VAC
0.5A @ 25VDC
- 5. CONTACT MATERIAL: SILVER
- 6. ELECTRICAL LIFE: 200,000 Typical
- 7. MECHANICAL LIFE:
1,000,000 CYCLES TYP.
- 8. OPERATING TEMP: -20°C TO +70°C
- 9. OPERATING FORCE: 200 ± 100 gf
- 10. CONTACT RESISTANCE:
50 MILLI-OHM INITIAL TYP. MAX.
- 11. DIELECTRIC STRENGTH:
1000 VAC FOR 1 MINUTE
- 12. TRAVEL TO MAKE: 2.20mm ± 0.2
- 13. 2002/95/EC (ROHS) COMPLIANT
- 14. ▲ DENOTES CRITICAL PARAMETER
- ▲ 15. LED COLOR: RED: 3 CHIPS; 1.7VDC, @20mA TYP.



E	19708	UPDATE DRAWING	02/23/11	BMA	TITLE ULP12OAP1QSSCL1REDNIL				
REV	PCR NO	DESCRIPTION	DATE	BY					
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED					SCALE 1.5:1	DATE 10/10/2007	DR BF	DWG B800001	REV E

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[ULP12OAP1QSSCL1REDNIL](#)