



Base unit (BU30-MS9) with F-DI forwarding For ET 200SP motor starter Without infeed

| | |
|--|--|
| product brand name | SIMATIC |
| product category | Accessories |
| product designation | BaseUnit |
| design of the product | without AC/DC infeed, with F-DI loop-through |
| product type designation | ET 200SP |
| General technical data | |
| insulation voltage rated value | 500 V |
| degree of pollution | 2 |
| surge voltage resistance rated value | 6 kV |
| maximum permissible voltage for protective separation <ul style="list-style-type: none"> • between main and auxiliary circuit | 500 V |
| shock resistance | 6g / 11 ms |
| vibration resistance | 15 mm to 6 Hz; 2g to 500 Hz |
| reference code according to IEC 81346-2 | Q |
| Substance Prohibition (Date) | 04/15/2016 |
| SVHC substance name | Lead monoxide (lead oxide) - 1317-36-8 |
| Weight | 170 g |
| Electrical Safety | |
| protection class IP on the front according to IEC 60529 | IP20 |
| touch protection on the front according to IEC 60529 | finger-safe |
| Main circuit | |
| number of poles for main current circuit | 3 |
| type of voltage of the operating voltage | AC |
| operating voltage rated value maximum | 500 V |
| operational current at AC at 400 V rated value | 32 A; Derating, see Manual |
| Inputs/ Outputs | |
| number of digital inputs | 0 |
| Supply voltage | |
| type of voltage of the supply voltage | DC |
| supply voltage 1 at DC rated value <ul style="list-style-type: none"> • minimum permissible • maximum permissible | 24 V 20.4 V 28.8 V |
| ampacity maximum | 7 A |
| Installation/ mounting/ dimensions | |
| mounting position | vertical, horizontal |
| fastening method | DIN rail |
| height | 215 mm |
| width | 30 mm |
| depth | 75 mm |
| required spacing with side-by-side mounting | |

| | |
|--|--|
| <ul style="list-style-type: none"> • upwards • downwards | 50 mm 50 mm |
| Ambient conditions | |
| installation altitude at height above sea level maximum | 4 000 m; For derating see manual |
| ambient temperature | |
| <ul style="list-style-type: none"> • during operation • during storage • during transport | -25 ... +60 °C; For derating see manual -40 ... +70 °C -40 ... +70 °C |
| environmental category during operation according to IEC 60721 | 3K6 (no formation of ice, no condensation), 3C3 (no salt mist), 3S2 (sand must not get into the devices) |
| relative humidity during operation | 10 ... 95 % |
| air pressure according to SN 31205 | 900 ... 1 060 hPa |

| | |
|--|--|
| Connections/ Terminals | |
| type of electrical connection | |
| <ul style="list-style-type: none"> • for main current circuit • for auxiliary and control circuit | spring-loaded terminals (push-in) spring-loaded terminals (push-in) |
| type of connecting terminal | Push-in terminal |
| type of connectable conductor cross-sections for load-side outgoing feeder | |
| <ul style="list-style-type: none"> • solid • finely stranded without core end processing • finely stranded with core end processing | 1x 0,5 ... 2,5 mm ² 1x 0,5 ... 2,5 mm ² 1x 0,5 ... 2,5 mm ² |
| type of connectable conductor cross-sections for AWG cables for load-side outgoing feeder | 1x 20 ... 12 |
| shape of the screwdriver tip | Slot |
| size of the screwdriver tip | Standard screwdriver 0.6 mm x 3.5 mm |

| | |
|---------------------------------|--------------------------|
| Approvals Certificates | |
| General Product Approval | Test Certificates |



[Confirmation](#)





[Type Test Certificates/Test Report](#)

| | | |
|--------------------------|-------------------------------------|--|
| Marine / Shipping | other | Environment |
| | <p>Confirmation</p> | <p>Environmental Confirmations</p> |

Further information

Information on the packaging
<https://support.industry.siemens.com/cs/ww/en/view/109813875>
Information- and Downloadcenter (Catalogs, Brochures,...)
<https://www.siemens.com/ic10>
Industry Mall (Online ordering system)
<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RK1908-0AP00-0JP0>
Cax online generator
<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RK1908-0AP00-0JP0>
Service&Support (Manuals, Certificates, Characteristics, FAQs,...)
<https://support.industry.siemens.com/cs/ww/en/ps/3RK1908-0AP00-0JP0>
Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)
http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RK1908-0AP00-0JP0&lang=en



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Siemens:](#)

[3RK19080AP000JP0](#)