



Selector switch, illuminable, 30 mm, round, Metal, matte, white, selector switch, short, front ring for flush installation, 3 switch positions I-O-II, latching, actuating angle 2x45°, 10:30h/12h/13:30h, Z=50-unit packaging

|                                                    |                                        |
|----------------------------------------------------|----------------------------------------|
| product brand name                                 | SIRIUS ACT                             |
| product designation                                | Selector switches                      |
| design of the product                              | Actuating/signaling element            |
| product type designation                           | 3SU1                                   |
| product line                                       | Metal, matt, flat, 30 mm               |
| <b>Enclosure</b>                                   |                                        |
| number of command points                           | 1                                      |
| <b>Actuator</b>                                    |                                        |
| design of the actuating element                    | Selector, short                        |
| principle of operation of the actuating element    | latching, 2x45° (10:30 h/12 h/13:30 h) |
| product extension optional                         |                                        |
| • light source                                     | Yes                                    |
| • contact module                                   | Yes                                    |
| color of the actuating element                     | white                                  |
| material of the actuating element                  | plastic                                |
| shape of the actuating element                     | Handle                                 |
| outer diameter of the actuating element            | 38 mm                                  |
| number of switching positions                      | 3                                      |
| actuating angle                                    |                                        |
| • clockwise                                        | 45°                                    |
| • anticlockwise                                    | 45°                                    |
| <b>Front ring</b>                                  |                                        |
| product component front ring                       | Yes                                    |
| design of the front ring                           | Flat                                   |
| material of the front ring                         | Metal, matt                            |
| color of the front ring                            | sand gray                              |
| <b>General technical data</b>                      |                                        |
| protection class IP                                | IP66, IP67, IP69(IP69K)                |
| degree of protection NEMA rating                   | 1, 2, 3, 3R, 4, 4X, 12, 13             |
| shock resistance                                   |                                        |
| • according to IEC 60068-2-27                      | sinusoidal half-wave 15g / 11 ms       |
| • for railway applications according to EN 61373   | Category 1, Class B                    |
| vibration resistance                               |                                        |
| • according to IEC 60068-2-6                       | 10 ... 500 Hz: 5g                      |
| • for railway applications according to EN 61373   | Category 1, Class B                    |
| operating frequency maximum                        | 1 800 1/h                              |
| mechanical service life (operating cycles) typical | 300 000                                |
| reference code according to IEC 81346-2            | S                                      |
| Substance Prohibitance (Date)                      | 10/01/2014                             |
| <b>Safety related data</b>                         |                                        |

|                                                                      |         |
|----------------------------------------------------------------------|---------|
| <b>proportion of dangerous failures</b>                              |         |
| • with low demand rate according to SN 31920                         | 20 %    |
| • with high demand rate according to SN 31920                        | 20 %    |
| <b>B10 value with high demand rate according to SN 31920</b>         | 300 000 |
| <b>failure rate [FIT] with low demand rate according to SN 31920</b> | 100 FIT |

|                                                                |                                                                    |
|----------------------------------------------------------------|--------------------------------------------------------------------|
| <b>Ambient conditions</b>                                      |                                                                    |
| <b>ambient temperature</b>                                     |                                                                    |
| • during operation                                             | -25 ... +70 °C                                                     |
| • during storage                                               | -40 ... +80 °C                                                     |
| environmental category during operation according to IEC 60721 | 3M6, 3S2, 3B2, 3C3, 3K6 (with relative air humidity of 10 ... 95%) |

|                                             |         |
|---------------------------------------------|---------|
| <b>Installation/ mounting/ dimensions</b>   |         |
| height                                      | 44.8 mm |
| width                                       | 38 mm   |
| shape of the installation opening           | round   |
| mounting diameter                           | 30.5 mm |
| positive tolerance of installation diameter | 0.5 mm  |
| mounting height                             | 22.1 mm |
| installation width                          | 38 mm   |
| installation depth                          | 32.1 mm |

|                               |  |
|-------------------------------|--|
| <b>Approvals Certificates</b> |  |
| General Product Approval      |  |



[Confirmation](#)



|                          |                          |
|--------------------------|--------------------------|
| <b>Test Certificates</b> | <b>Marine / Shipping</b> |
|--------------------------|--------------------------|

[Type Test Certificates/Test Report](#)

[Special Test Certificate](#)



|              |                    |
|--------------|--------------------|
| <b>other</b> | <b>Environment</b> |
|--------------|--------------------|

[Confirmation](#)

[Environmental Confirmations](#)

|                            |
|----------------------------|
| <b>Further information</b> |
|----------------------------|

#### Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

#### Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

#### Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SU1062-2DL60-0AA0-Z X90>

#### Cax online generator


<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SU1062-2DL60-0AA0-Z X90>

#### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3SU1062-2DL60-0AA0-Z X90>

#### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=3SU1062-2DL60-0AA0-Z X90&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SU1062-2DL60-0AA0-Z X90&lang=en)



last modified:

1/26/2022 

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Siemens:](#)

[A6X30141307](#)