



Timing relay, electronic ON delay 1 change-over contact, 1 time range 5...100 s 24 V/230 V AC and 24 V DC with LED, Screw terminal

product brand name	SIRIUS
product designation	timing relay
design of the product	slow-operating
product type designation	7PV15
General technical data	
product component semi-conductor output	No
product extension required remote control	No
product extension optional remote control	No
insulation voltage for overvoltage category III according to IEC 60664 with degree of pollution 3 rated value	300 V
test voltage for isolation test	2.2 kV
degree of pollution	2
surge voltage resistance rated value	4 000 V
test voltage for surge voltage test	4 800 V
protection class IP	IP20
shock resistance according to IEC 60068-2-27	11g / 15 ms
vibration resistance according to IEC 60068-2-6	10 ... 55 Hz: 0.35 mm
mechanical service life (operating cycles) typical	10 000 000
electrical endurance (operating cycles) at AC-15 at 230 V typical	100 000
adjustable time	5 ... 100 s
relative setting accuracy relating to full-scale value	5 %; +/-
minimum ON period	35 ms
recovery time	500 ms
reference code according to IEC 81346-2	K
relative repeat accuracy	2 %; +/-
influence of the surrounding temperature	2% in complete temperature range for the set duration
power supply influence	2% in complete voltage range for the set duration
Substance Prohibitance (Date)	05/01/2012
Control circuit/ Control	
type of voltage of the control supply voltage	AC/DC
control supply voltage 1 at AC	
• at 50 Hz	200 ... 240 V
• at 60 Hz	200 ... 240 V
control supply voltage 2 at AC	
• at 50 Hz rated value	24 V
• at 60 Hz rated value	24 V
control supply voltage frequency 1	50 ... 60 Hz
control supply voltage 1	
• at DC rated value	24 V
operating range factor control supply voltage rated value at	

DC	• initial value	0.85
	• full-scale value	1.1
operating range factor control supply voltage rated value at AC at 50 Hz	• initial value	0.85
	• full-scale value	1.1
operating range factor control supply voltage rated value at AC at 60 Hz	• initial value	0.85
	• full-scale value	1.1
Switching Function		
switching function	• ON-delay	Yes
	• ON-delay/instantaneous contact	No
	• passing make contact	No
	• passing make contact/instantaneous contact	No
	• OFF delay	No
switching function	• flashing symmetrically with interval start/instantaneous	No
	• flashing symmetrically with interval start	No
	• flashing symmetrically with pulse start/instantaneous	No
	• flashing symmetrically with pulse start	No
	• flashing asymmetrically with interval start	No
	• flashing asymmetrically with pulse start	No
switching function	• star-delta circuit with delay time	No
	• star-delta circuit	No
switching function with control signal	• additive ON-delay	No
	• passing break contact	No
	• passing break contact/instantaneous	No
	• OFF delay	No
	• OFF delay/instantaneous	No
	• pulse delayed	No
	• pulse delayed/instantaneous	No
	• pulse-shaping	No
	• pulse-shaping/instantaneous	No
	• additive ON-delay/instantaneous	No
	• ON-delay/OFF-delay	No
	• ON-delay/OFF-delay/instantaneous	No
	• passing make contact	No
	• passing make contact/instantaneous contact	No
switching function of interval relay with control signal	• retrotriggerable with deactivated control signal/instantaneous contact	No
	• retrotriggerable with switched-on control signal	No
	• retrotriggerable with switched-on control signal/instantaneous contact	No
	• retriggrable with deactivated control signal	No
design of the control terminal non-floating		No
Short-circuit protection		
design of the fuse link for short-circuit protection of the auxiliary switch required		fuse gL/gG: 4 A
Auxiliary circuit		
material of switching contacts		AgSnO2
number of NC contacts	• delayed switching	0
	• instantaneous contact	0
number of NO contacts	• delayed switching	0
	• instantaneous contact	0

number of CO contacts	
• delayed switching	1
• instantaneous contact	0
operational current of auxiliary contacts at AC-15	
• maximum	3 A
• at 24 V	3 A
• at 250 V	3 A
operational current of auxiliary contacts as NC contact at AC-15	
• at 24 V	3 A
• at 250 V	3 A
operational current of auxiliary contacts as NO contact at AC-15	
• at 24 V	3 A
• at 250 V	3 A
operational current of auxiliary contacts at DC-13	1 ... 0.01
operational current of auxiliary contacts at DC-13	
• at 24 V	1 A
• at 125 V	0.22 A
• at 250 V	0.1 A
operating frequency with 3RT2 contactor maximum	5 000 1/h
contact reliability of auxiliary contacts	one incorrect switching operation of 100 million switching operations (17 V, 5 mA)
contact rating of auxiliary contacts according to UL	R150 / B300
switching capacity current with inductive load	0.01 ... 3 A
Inputs/ Outputs	
product function	
• at the relay outputs switchover delayed/without delay	No
• non-volatile	No
Electromagnetic compatibility	
EMC immunity according to IEC 61812-1	EN 61000-6-2
conducted interference	
• due to burst according to IEC 61000-4-4	2 kV network connection / 1 kV control connection
• due to conductor-earth surge according to IEC 61000-4-5	2 kV
• due to conductor-conductor surge according to IEC 61000-4-5	1 kV
field-based interference according to IEC 61000-4-3	10 V/m
electrostatic discharge according to IEC 61000-4-2	4 kV contact discharge / 8 kV air discharge
Safety related data	
type of insulation	Basic insulation
category according to EN 954-1	none
Connections/ Terminals	
product component removable terminal for auxiliary and control circuit	No
type of electrical connection for auxiliary and control circuit	screw-type terminals
type of connectable conductor cross-sections	
• solid	1x (0.2 ... 2.5 mm ²)
• finely stranded with core end processing	1x (0.25 ... 1.5 mm ²)
• finely stranded without core end processing	1x (0.2 ... 1.5 mm ²)
• for AWG cables solid	1x (24 ... 14)
• for AWG cables stranded	1x (24 ... 14)
connectable conductor cross-section	
• solid	0.2 ... 2.5 m ²
• finely stranded with core end processing	0.25 ... 1.5 m ²
• finely stranded without core end processing	0.2 ... 1.5 m ²
AWG number as coded connectable conductor cross section	
• solid	24 ... 14
• stranded	24 ... 14
Installation/ mounting/ dimensions	
mounting position	any
fastening method	snap-on fastening on 35 mm DIN rail

height	90 mm
width	17.5 mm
depth	66.7 mm
required spacing	
• with side-by-side mounting	
— forwards	0 mm
— backwards	0 mm
— upwards	0 mm
— downwards	0 mm
— at the side	0 mm
• for grounded parts	
— forwards	0 mm
— backwards	0 mm
— upwards	0 mm
— at the side	0 mm
— downwards	0 mm
• for live parts	
— forwards	0 mm
— backwards	0 mm
— upwards	0 mm
— downwards	0 mm
— at the side	0 mm

Ambient conditions	
installation altitude at height above sea level maximum	2 000 m
ambient temperature	
• during operation	-25 ... +55 °C
• during storage	-40 ... +70 °C
• during transport	-40 ... +70 °C
relative humidity during operation	15 ... 85 %

Certificates/ approvals		
General Product Approval	EMC	Declaration of Con- formity



[Confirmation](#)



Declaration of Con- formity	Test Certificates	other	Environment
--------------------------------	-------------------	-------	-------------



[Type Test Certificates/Test Report](#)

[Confirmation](#)

[Environmental Con-
firmations](#)

Further information

Siemens has decided to exit the Russian market (see here).

<https://press.siemens.com/global/en/pressrelease/siemens-wind-down-russian-business>

Siemens is working on the renewal of the current EAC certificates.

Please contact your local Siemens office on the status of validity of the EAC certification if you intend to import or offer to supply these products to an EAC relevant market (other than the sanctioned EAEU member states Russia or Belarus).

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=7PV1513-1AP30>

Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=7PV1513-1AP30>


Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/7PV1513-1AP30>


Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=7PV1513-1AP30&lang=en

Characteristic: Derating



Alle Bemessungswerte sind in Millimeter (mm) angegeben
All dimensions are in millimeters (mm)



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

7PV15131AP30