

SCALANCE XR324-4M PoE TS; Managed IE switch, 19" rack; 8x 10/100/1000 Mbit/s for RJ45 ports electrical with PoE, 8x 10/100/1000 Mbit/s for RJ45 ports electrical without PoE; 4x 10/100/1000 Mbit/s 2-port media modules, electrical or optical; LED diagnostics; error signaling Contact; Select/set pushbutton, PROFINET IO device, Power supply 24 V DC; Ports in the front.



product type designation	SCALANCE XR324-4M PoE TS
transfer rate	
transfer rate	10 Mbit/s, 100 Mbit/s, 1000 Mbit/s
interfaces / for communication / maximum configuration for modular devices	
number of electrical ports / maximum	24
number of electrical ports / with PoE / maximum	8
number of optical ports / maximum	8
interfaces / for communication / integrated	
number of electrical connections	
• for network components or terminal equipment	16; RJ45
• for Power-over-Ethernet / for network components or terminal equipment	8
number of 100 Mbit/s ST(BFOC) ports	
• for multimode	8
number of 100 Mbit/s SC ports	
• for multimode	8
number of 1000 Mbit/s LC ports	
• for multimode	8
• for single mode (LD)	8
interfaces / other	
number of electrical connections	
• for operator console	1
• for signaling contact	1
• for media module	4
• for power supply	1
type of electrical connection	
• for operator console	RJ11
• for signaling contact	2-pole terminal block
• for power supply	4-pole terminal block
design of the removable storage	
• C-PLUG	Yes
signal inputs/outputs	
operating voltage / of the signaling contacts	
• at DC / rated value	24 V
operational current / of the signaling contacts	
• at DC / maximum	0.1 A
supply voltage, current consumption, power loss	
product component / connection for redundant voltage supply	Yes
type of voltage supply / redundant power supply unit	No
type of voltage / 1 / of the supply voltage	DC

<ul style="list-style-type: none"> • supply voltage / 1 / rated value • power loss [W] / 1 / rated value • supply voltage / 1 / rated value • consumed current / 1 / maximum • type of electrical connection / 1 / for power supply • product component / 1 / fusing at power supply input 	24 V 46 W 19.2 ... 28.8 V 4.2 A 4-pole terminal block Yes
ambient conditions	
ambient temperature <ul style="list-style-type: none"> • during operation • during storage • during transport • note 	-40 ... +70 °C -40 ... +85 °C -40 ... +85 °C With vertical installation, the maximum operating temperature is reduced to 60 °C.
relative humidity <ul style="list-style-type: none"> • at 25 °C / without condensation / during operation / maximum 	95 %
protection class IP	IP20
design, dimensions and weights	
design	19" rack
number of modular height units / relating to 19-inch cabinet	1
width	449 mm
height	43.6 mm
depth	305 mm
net weight	6.8 kg
product feature / conformal coating	Yes
fastening method <ul style="list-style-type: none"> • 19-inch installation • 35 mm top hat DIN rail mounting • wall mounting • S7-300 rail mounting • S7-1500 rail mounting 	When used in shipbuilding, the device must be secured in the 19" rack at four points Yes No No No No
product features, product functions, product components / general	
cascading in the case of a redundant ring / at reconfiguration time of <1~0.3~s	100
cascading in cases of star topology	any (depending only on signal propagation time)
product functions / management, configuration, engineering	
product function <ul style="list-style-type: none"> • CLI • web-based management • MIB support • TRAPs via email • configuration with STEP 7 • RMON • port mirroring • multiport mirroring • CoS • PROFINET IO diagnosis 	Yes Yes Yes Yes Yes Yes Yes Yes Yes Yes
PROFINET conformity class	B
product function / switch-managed	Yes
protocol / is supported <ul style="list-style-type: none"> • Telnet • HTTP • HTTPS • TFTP • FTP • BOOTP • GMRP • DCP • LLDP • SNMP v1 • SNMP v2 	Yes Yes Yes Yes Yes Yes Yes Yes Yes Yes Yes

• SNMP v3	Yes
• IGMP (snooping/querier)	Yes
identification & maintenance function	
• I&M0 - device-specific information	Yes
• I&M1 - higher level designation/location designation	Yes
product functions / diagnostics	
product function	
• port diagnostics	Yes
• statistics Packet Size	Yes
• statistics packet type	Yes
• error statistics	Yes
• SysLog	Yes
product functions / VLAN	
product function	
• VLAN - port based	Yes
• VLAN - protocol-based	No
• VLAN - IP-based	No
• VLAN dynamic	Yes
number of VLANs / maximum	255
number of VLANs - dynamic / maximum	255
protocol / is supported / GVRP	Yes
product functions / DHCP	
product function	
• DHCP client	Yes
• DHCP Option 82	Yes
• DHCP Option 66	Yes
• DHCP Option 67	Yes
product functions / redundancy	
product function	
• ring redundancy	Yes
• High Speed Redundancy Protocol (HRP)	Yes
• high speed redundancy protocol (HRP) with redundancy manager	Yes
• high speed redundancy protocol (HRP) with standby redundancy	Yes
protocol / is supported / Media Redundancy Protocol (MRP)	Yes
product function	
• media redundancy protocol (MRP) with redundancy manager	Yes
• redundancy procedure STP	Yes
• redundancy procedure RSTP	Yes
• redundancy procedure MSTP	Yes
• passive listening	Yes
protocol / is supported	
• STP/RSTP	Yes
• STP	Yes
• RSTP	Yes
• MSTP	Yes
• RSTP big network support	Yes
• LACP	Yes
product functions / security	
product function	
• ACL - MAC-based	Yes
• ACL - port/MAC-based	Yes
• IEEE 802.1x (radius)	Yes
• broadcast/multicast/unicast limiter	Yes
• broadcast blocking	Yes
protocol / is supported	
• SSH	Yes
product functions / time	
product function	

<ul style="list-style-type: none"> • SICLOCK support 	Yes
protocol / is supported	
<ul style="list-style-type: none"> • NTP 	Yes
<ul style="list-style-type: none"> • SNTP 	Yes
<ul style="list-style-type: none"> • IEEE 1588 profile default 	Yes
standards, specifications, approvals	
standard	
<ul style="list-style-type: none"> • for FM 	FM3611: Class 1, Division 2, Group A, B, C, D / T4, Class 1, Zone 2, Group IIC, T4
<ul style="list-style-type: none"> • for safety / from CSA and UL 	UL 60950-1, CSA C22.2 No. 60950-1
<ul style="list-style-type: none"> • for emitted interference 	EN 61000-6-4:2007 (Class A)
<ul style="list-style-type: none"> • for interference immunity 	EN 61000-6-2:2006
reference code	
<ul style="list-style-type: none"> • according to IEC 81346-2 	KF
<ul style="list-style-type: none"> • according to IEC 81346-2:2019 	KFE
standards, specifications, approvals / CE	
certificate of suitability / CE marking	Yes
standards, specifications, approvals / hazardous environments	
standard / for hazardous zone	EN 60079-0 : 2006, EN 60079-15: 2005, II 3 G Ex nA II T4 KEMA 07 ATEX 0145X
<ul style="list-style-type: none"> • from CSA and UL 	UL 1604 and UL 2279-15 (Hazardous Location), CSA C22.2 No. 213-M1987, Class 1 / Division 2 / Group A, B, C, D / T4, Class 1 / Zone 2 / Group IIC / T4
certificate of suitability	
<ul style="list-style-type: none"> • CCC / for hazardous zone according to GB standard 	Yes
<ul style="list-style-type: none"> • CCC / for hazardous zone according to GB standard / as marking 	Ex nA IIC T4 Gc
standards, specifications, approvals / other	
certificate of suitability	EN 61000-6-2:2006, EN 61000-6-4:2007
<ul style="list-style-type: none"> • C-Tick 	Yes
<ul style="list-style-type: none"> • KC approval 	Yes
<ul style="list-style-type: none"> • railway application in accordance with EN 50155 	Yes
<ul style="list-style-type: none"> • railway application in accordance with EN 50121-4 	Yes
standards, specifications, approvals / marine classification	
Marine classification association	
<ul style="list-style-type: none"> • French marine classification society (BV) 	Yes
<ul style="list-style-type: none"> • Korean Register of Shipping (KRS) 	Yes
further information / internet links	
internet link	
<ul style="list-style-type: none"> • to web page: selection aid TIA Selection Tool 	http://www.siemens.com/tia-selection-tool
<ul style="list-style-type: none"> • to website: Industrial communication 	http://www.siemens.com/simatic-net
<ul style="list-style-type: none"> • to website: Industry Mall 	https://mall.industry.siemens.com
<ul style="list-style-type: none"> • to website: Information and Download Center 	http://www.siemens.com/industry/infocenter
<ul style="list-style-type: none"> • to website: Image database 	http://automation.siemens.com/bilddb
<ul style="list-style-type: none"> • to website: CAX-Download-Manager 	http://www.siemens.com/cax
<ul style="list-style-type: none"> • to website: Industry Online Support 	https://support.industry.siemens.com
security information	
security information	Siemens provides products and solutions with industrial security functions that support the secure operation of plants, solutions, machines, equipment and/or networks. They are important components in a holistic industrial security concept. With this in mind, Siemens' products and solutions undergo continuous development. Siemens recommends strongly that you regularly check for product updates. For the secure operation of Siemens products and solutions, it is necessary to take suitable preventive action(e.g. cell protection concept) and integrate each component into a holistic, state-of-the-art industrial security concept. Third-party products that may be in use should also be considered. For more information about industrial security, visit http://www.siemens.com/industrialsecurity . To stay informed about product updates as they occur, sign up for a product-specific newsletter. For more information, visit http://support.automation.siemens.com . (V3.4)

last modified:

8/18/2023 

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

[6GK53244QG101CR2](#)