

SCALANCE XR326-2C PoE WG; managed IE Switch; 19" rack; 24 x 1GE electrical PoE ports 2 x 10GE electrical combo PoE ports; electrical o. optical; LED diagnostics; reset button; console port; PROFINET device; network management function; Redundancy Manager; power supply 240 V AC (85 – 264 V).



<b>product type designation</b>	<b>SCALANCE XR326-2C PoE WG</b>
<b>transfer rate</b>	
transfer rate	10 Mbit/s, 100 Mbit/s, 1000 Mbit/s, 2.5 Gbit/s, 5 Gbit/s, 10 Gbit/s
<b>interfaces / for communication / maximum configuration for modular devices</b>	
number of electrical ports / maximum	26
number of electrical ports / with PoE / maximum	26
number of optical ports / maximum	2
<b>interfaces / for communication / integrated</b>	
number of electrical connections	
• for network components or terminal equipment	26; RJ45
• for Power-over-Ethernet / for network components or terminal equipment	26
number of 10/100/1000 Mbit/s RJ45 ports / integrated	
• with PoE	24; PoE Ports according to IEEE802.3at (30 W)
number of 10/100/1000/10000 Mbit/s RJ45 ports / integrated / with PoE	2; PoE Ports according to IEEE802.3bt (60 W) executed as combo port
number of combo ports / with RJ45 interface for optical plug-in transceiver	2; 1000 Mbit/s, 2500 Mbit/s, 5000 Mbit/s, 10000 Mbit/s RJ45 port incl. PoE function and 1000 Mbit/s, 10000 Mbit/s SFP port
<b>interfaces / other</b>	
number of electrical connections	
• for operator console	1
• for power supply	2
type of electrical connection	
• for operator console	RJ11
• for power supply	IEC plug C14 and terminal block for additional PoE power supply (max. 2 additional PSR9230PoE possible, PoE power expandable to 570W)
<b>supply voltage, current consumption, power loss</b>	
product component / power supply for PoE	Yes
product feature	
• modular power supply	Yes
supplied active power / of PSE / with PoE	
• total / maximum	210 W
<b>type of voltage / 1 / of the supply voltage</b>	
• supply voltage / 1 / rated value	240 V
• supply voltage / 1 / rated value	85 ... 264 V
• consumed current / 1 / maximum	4 A
• product component / 1 / fusing at power supply input	Yes
<b>ambient conditions</b>	
ambient temperature	
• during operation	0 ... 60 °C
• during storage	-40 ... +85 °C

• during transport	-40 ... +85 °C
relative humidity	
• at 25 °C / without condensation / during operation / maximum	95 %
protection class IP	IP30
<b>design, dimensions and weights</b>	
design	19" rack
number of modular height units / relating to 19-inch cabinet	1
width	482.6 mm
height	43.6 mm
depth	227.3 mm
net weight	4.7 kg
material / of the enclosure	metal
fastening method	
• 19-inch installation	Yes
• 35 mm top hat DIN rail mounting	No
• wall mounting	No
• S7-300 rail mounting	No
• S7-1500 rail mounting	No
<b>product features, product functions, product components / general</b>	
cascading in the case of a redundant ring / at reconfiguration time of <~0.3~s	50
cascading in cases of star topology	any (depending only on signal propagation time)
<b>product functions / management, configuration, engineering</b>	
product function	
• CLI	Yes
• web-based management	Yes
• MIB support	Yes
• TRAPs via email	Yes
• configuration with STEP 7	Yes
• RMON	Yes
• port mirroring	Yes
• multiport mirroring	No
• CoS	Yes
• PROFINET IO diagnosis	Yes
PROFINET conformity class	B
network load class / according to PROFINET	3
product function / switch-managed	Yes
protocol / is supported	
• Telnet	Yes
• HTTP	Yes
• HTTPS	Yes
• TFTP	Yes
• FTP	Yes
• BOOTP	Yes
• GMRP	No
• DCP	Yes
• LLDP	Yes
• SNMP v1	Yes
• SNMP v2	Yes
• SNMP v3	Yes
• IGMP (snooping/querier)	Yes
identification & maintenance function	
• I&M0 - device-specific information	Yes
• I&M1 - higher level designation/location designation	Yes
<b>product functions / diagnostics</b>	
product function	
• port diagnostics	Yes
• statistics Packet Size	Yes
• statistics packet type	Yes
• error statistics	Yes

• SysLog	Yes
<b>product functions / VLAN</b>	
product function	
• VLAN - port based	Yes
• VLAN - protocol-based	No
• VLAN - IP-based	No
• VLAN dynamic	Yes
number of VLANs / maximum	257
number of VLANs - dynamic / maximum	257
number of VLANs / at ring redundancy (HRP; MRP; standby link)	257
protocol / is supported / GVRP	No
<b>product functions / DHCP</b>	
product function	
• DHCP client	Yes
• DHCP Option 82	Yes
• DHCP Option 66	Yes
• DHCP Option 67	Yes
<b>product functions / redundancy</b>	
product function	
• ring redundancy	Yes
• High Speed Redundancy Protocol (HRP)	Yes
• high speed redundancy protocol (HRP) with redundancy manager	Yes
• high speed redundancy protocol (HRP) with standby redundancy	Yes
protocol / is supported / Media Redundancy Protocol (MRP)	Yes
product function	
• media redundancy protocol (MRP) with redundancy manager	Yes
• of the PROFINET IO device / is supported / H-Sync forwarding	No
• redundancy procedure STP	Yes
• redundancy procedure RSTP	Yes
• redundancy procedure MSTP	No
• Parallel Redundancy Protocol (PRP)/operation in the PRP-network	Yes
• Parallel Redundancy Protocol (PRP)/Redundant Network Access (RNA)	No
• passive listening	Yes
protocol / is supported	
• STP/RSTP	Yes
• STP	Yes
• RSTP	Yes
• MSTP	No
• RSTP big network support	Yes
• LACP	No
<b>product functions / security</b>	
product function	
• ACL - MAC-based	Yes
• ACL - port/MAC-based	Yes
• IEEE 802.1x (radius)	Yes
• broadcast/multicast/unicast limiter	Yes
• broadcast blocking	Yes
protocol / is supported	
• SSH	Yes
<b>product functions / time</b>	
product function	
• SICLOCK support	Yes
• SNTP client	Yes
protocol / is supported	
• NTP	Yes

<ul style="list-style-type: none"> <li>• SNTP</li> <li>• IEEE 1588 profile default</li> </ul>	Yes No
<b>system modification during operation</b>	
product function / configuration in RUN via CiR/H-CiR	No
<b>standards, specifications, approvals</b>	
standard <ul style="list-style-type: none"> <li>• for safety / from CSA and UL</li> <li>• for emitted interference</li> <li>• for interference immunity</li> </ul>	UL 62368-1, CSA C22.2 No. 62368-1 EN 61000-6-4 EN 61000-6-2
IT security for industrial automation systems / according to IEC 62443-4-2:2019	Yes
MTBF	25 a
reference code <ul style="list-style-type: none"> <li>• according to IEC 81346-2</li> <li>• according to IEC 81346-2:2019</li> </ul>	KF KFE
<b>standards, specifications, approvals / CE</b>	
certificate of suitability / CE marking	Yes
<b>standards, specifications, approvals / other</b>	
certificate of suitability <ul style="list-style-type: none"> <li>• C-Tick</li> <li>• KC approval</li> <li>• railway application in accordance with EN 50155</li> <li>• EAC approval</li> </ul>	Yes Yes No Yes
<b>accessories</b>	
accessories	PSR9230PoE
<b>further information / internet links</b>	
internet link <ul style="list-style-type: none"> <li>• to web page: selection aid TIA Selection Tool</li> <li>• to website: Industrial communication</li> <li>• to website: Industry Mall</li> <li>• to website: Information and Download Center</li> <li>• to website: Image database</li> <li>• to website: CAX-Download-Manager</li> <li>• to website: Industry Online Support</li> </ul>	<a href="http://www.siemens.com/tia-selection-tool">http://www.siemens.com/tia-selection-tool</a> <a href="http://www.siemens.com/simatic-net">http://www.siemens.com/simatic-net</a> <a href="https://mall.industry.siemens.com">https://mall.industry.siemens.com</a> <a href="http://www.siemens.com/industry/infocenter">http://www.siemens.com/industry/infocenter</a> <a href="http://automation.siemens.com/bilddb">http://automation.siemens.com/bilddb</a> <a href="http://www.siemens.com/cax">http://www.siemens.com/cax</a> <a href="https://support.industry.siemens.com">https://support.industry.siemens.com</a>
<b>security information</b>	
security information	<p>Siemens provides products and solutions with industrial security functions that support the secure operation of plants, solutions, machines, equipment and/or networks. They are important components in a holistic industrial security concept. With this in mind, Siemens' products and solutions undergo continuous development. Siemens recommends strongly that you regularly check for product updates. For the secure operation of Siemens products and solutions, it is necessary to take suitable preventive action (e.g. cell protection concept) and integrate each component into a holistic, state-of-the-art industrial security concept. Third-party products that may be in use should also be considered. For more information about industrial security, visit <a href="http://www.siemens.com/industrialsecurity">http://www.siemens.com/industrialsecurity</a>. To stay informed about product updates as they occur, sign up for a product-specific newsletter. For more information, visit <a href="http://support.automation.siemens.com">http://support.automation.siemens.com</a>. (V3.4)</p>

last modified:

4/21/2023 

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

[6GK53262QS003AR3](#)