

**Modlight50 Pro connecting modul tube mounting**

Input 24VDC

Art.No.: 4000-76050-1100003

Weight: 0.1

Country of origin: ID

Model designation: Modlight50 Pro TUBE MOUNTING

Basic for tube mounting

Connection cables are in the online shop under "Connection Technology".

**[Link to Product](#)****Illustration**

Product may differ from Image

**Commercial data**

ECLASS-6.0	27371232
ECLASS-6.1	27371232
ECLASS-7.0	27371232
ECLASS-8.0	27371232
ECLASS-9.0	27371232
ECLASS-10.1	27371232
ECLASS-11.1	27371232
ECLASS-12.0	27371232
ETIM-5.0	EC001152
ETIM-6.0	EC001152
ETIM-7.0	EC001152
customs tariff number	85319000
GTIN	4048879751513
Packaging unit	1

**Electrical data | Supply**

Operating voltage DC	24 V
Operating voltage DC min.	21,6 V
Operating voltage DC max.	26,4 V

**Device protection | Electrical**

The information in this Product-PDF has been compiled with the utmost care.

Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2024-12-17

Murrelektronik Inc. | 1327 Northbrook Parkway, Suite 460 | Suwanee, GA 30024 | Fon +1 770 497-9292 | Fax +1 770 497-9391 | shop@murrinc.com | shop.murrinc.com

Degree of protection (EN IEC 60529)	IP65
Additional condition protection degree	inserted, locked
<b>Mechanical data   Material data</b>	
Color housing	black
Material housing	Plastic
<b>Mechanical data   Mounting data</b>	
Height	180 mm
Width	50 mm
Depth	50 mm
<b>Environmental characteristics   Climatic</b>	
Operating temperature min.	-30 °C
Operating temperature max.	60 °C
<b>Connection type 1</b>	
Connection	Spring clamp terminals FK
Family construction form	terminal
Gender	female
No. of poles	9
PIN 1	LED-Modul RD
PIN 2	LED-Modul YE
PIN 3	LED-Modul GN
PIN 4	LED-Modul BU
PIN 5	LED-Modul CL
PIN 6	Buzzer
PIN 7	24 V DC (0 V)
PIN 8	Blinking
PIN 9	0 V (24 V DC)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Murrelektronik:](#)

[4000-76050-1100003](#)