

IMPACT67 COMPACT MODULE, PLASTIC

Profinet, 16 dig. Out

Art.No.: 55094
Weight: 0.44
Country of origin: DE
Model designation: Impact67 PN DO16


Digital outputs
DO16 - 0.5 A
Ethernet 10/100 Mbit/s; M12, D-coded
7/8", 5-pole, 2× max. 9 A
M12, 5-pole, A-coded
Connection cables are in the online shop under "Connection Technology".
Housing fully potted.
mounting compatible with I/O modules of the MVK series

Link to Product

Illustration



Product may differ from Image



Commercial data	
ECLASS-6.0	27242604
ECLASS-6.1	27242604
ECLASS-7.0	27242604
ECLASS-8.0	27242604
ECLASS-9.0	27242604
ECLASS-10.1	27242604
ECLASS-11.1	27242604
ECLASS-12.0	27242604
ETIM-5.0	EC001599
customs tariff number	85389099
GTIN	4048879051880
Packaging unit	1
Electrical data Supply	

Total current UA max.	9 A
-----------------------	-----

Total current US max.	9 A
-----------------------	-----

Electrical data | Output

Overload resistant	yes
--------------------	-----

Short-circuit protected	yes
-------------------------	-----

Output current per pin max.	0,5 A
-----------------------------	-------

Industrial communication | Profinet

PROFINET addressing	DCP
---------------------	-----

Diagnostics

Diagnostic	No voltage, Under voltage
------------	---------------------------

Diagnostic via BUS	per module and channel
--------------------	------------------------

Diagnostic via LED	per module and channel
--------------------	------------------------

LED display	Ethernet connection/data traffic
-------------	----------------------------------

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP67
-------------------------------------	------

Mechanical data | Mounting data

Suitable for mounting type	2-hole screw mounting
----------------------------	-----------------------

Height	39 mm
--------	-------

Width	63 mm
-------	-------

Depth	225 mm
-------	--------

Environmental characteristics | Climatic

Operating temperature min.	-25 °C
----------------------------	--------

Operating temperature max.	55 °C
----------------------------	-------

Storage temperature min.	-25 °C
--------------------------	--------

Storage temperature max.	70 °C
--------------------------	-------

Connection type 4

Connection type 1	0-7
-------------------	-----

Connection type 2	Port1, Port2
-------------------	--------------

Connection type 3	Power In
-------------------	----------

Connection type 4	Power Out
-------------------	-----------

Family construction form	M12
--------------------------	-----

Gender	female
--------	--------

Color contact carrier	black
-----------------------	-------

Coding	A
--------	---

No. of poles	5
--------------	---

PIN 1	n.c.
-------	------

PIN 2	DO 10-17
-------	----------

PIN 3	0 V
-------	-----

PIN 4	DO 00-07
-------	----------

PIN 5	PE
-------	----

Mounting method	inserted, screwed
-----------------	-------------------

Tightening torque	0,6 Nm
-------------------	--------

Family construction form	M12
--------------------------	-----

Gender	female
--------	--------

Color contact carrier	black
-----------------------	-------

Coding	D
--------	---

No. of poles	4
--------------	---

PIN 1	TD +
-------	------

PIN 2	RD +
-------	------

PIN 3	TD -
-------	------

PIN 4	RD -
-------	------

Family construction form	7/8"
Gender	male
Color contact carrier	black
No. of poles	5
PIN 1	0 V
PIN 2	0 V
PIN 3	PE
PIN 4	24 V DC (US)
PIN 5	24 V DC (UA)
Family construction form	7/8"
Gender	female
Color contact carrier	black
No. of poles	5
PIN 1	0 V
PIN 2	0 V
PIN 3	PE
PIN 4	24 V DC (US)
PIN 5	24 V DC (UA)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Murrelektronik:](#)

[55094](#)