

MVK E/A KOMPAKTMODUL, METALLAUSFÜHRUNG

Profibus DP, 16 dig. Aus

Art.No.: 55290

Weight: 0.82

Country of origin: DE

Model designation: MVK-MP DO8 (DO8)

Digital outputs

DO8 DO8

PROFIBUS 12 Mbit/s; M12, B-coded

7/8", 5-pole, 2x max. 9 A

M12, 5-pole, A-coded

Connection cables are in the online shop under "Connection Technology".


Housing fully potted.

[Link to Product](#)

Illustration



Product may differ from Image



Commercial data

| | |
|-----------------------|---------------|
| ECLASS-6.0 | 27242604 |
| ECLASS-6.1 | 27242604 |
| ECLASS-7.0 | 27242604 |
| ECLASS-8.0 | 27242604 |
| ECLASS-9.0 | 27242604 |
| ECLASS-10.1 | 27242604 |
| ECLASS-11.1 | 27242604 |
| ECLASS-12.0 | 27242604 |
| ETIM-5.0 | EC001599 |
| customs tariff number | 85389099 |
| GTIN | 4048879051613 |
| Packaging unit | 1 |

Electrical data | Supply

| | |
|-------------------------|------------|
| Norm operating voltage | EN 61131-2 |
| Operating voltage UA DC | 24 V |

| | |
|---|----------------------------------|
| Total current UA max. | 9 A |
| Total current US max. | 9 A |
| Electrical data Output | |
| Overload resistant | yes |
| Short-circuit protected | yes |
| Output current per pin max. | 1,6 A |
| Lamp load | 10 W |
| Industrial communication Bus data | |
| Address range min. | 1 |
| Address range max. | 99 |
| Address setting type | Rotary switch |
| Diagnostics | |
| Actuator warning | per channel via LED and BUS |
| Diagnostic | No voltage, Under voltage |
| Diagnostic via BUS | per module and channel |
| Diagnostic via LED | per module and channel |
| Short circuit diagnosis | yes |
| LED display | Ethernet connection/data traffic |
| Cable break | per port |
| Overload diagnosis | yes |
| Device protection Electrical | |
| Degree of protection (EN IEC 60529) | IP67 |
| Mechanical data Mounting data | |
| Suitable for mounting type | 2-hole screw mounting |
| Height | 42 mm |
| Width | 63 mm |
| Depth | 225 mm |
| Environmental characteristics Climatic | |
| Operating temperature min. | -25 °C |
| Operating temperature max. | 55 °C |
| Storage temperature min. | -25 °C |
| Storage temperature max. | 70 °C |
| Connection type 6 | |
| Connection type 1 | 0-3 |
| Connection type 2 | 4-7 |
| Connection type 3 | Bus In |
| Connection type 4 | Bus Out |
| Connection type 5 | Power In |
| Connection type 6 | Power Out |
| Family construction form | M12 |
| Gender | female |
| Color contact carrier | black |
| Coding | A |
| No. of poles | 5 |
| PIN 1 | n.c. |
| PIN 2 | DO |
| PIN 3 | 0 V (UA) |
| PIN 4 | DO |
| PIN 5 | PE |
| Family construction form | M12 |
| Gender | female |

| | |
|--------------------------|--------------|
| Color contact carrier | black |
| Coding | A |
| No. of poles | 5 |
| PIN 1 | 24 V DC (US) |
| PIN 2 | DI / Diag |
| PIN 3 | 0 V (US) |
| PIN 4 | DI |
| PIN 5 | PE |
| Family construction form | M12 |
| Gender | male |
| Color contact carrier | black |
| Coding | B |
| No. of poles | 5 |
| PIN 1 | n.c. |
| PIN 2 | A GN |
| PIN 3 | n.c. |
| PIN 4 | B RD |
| PIN 5 | n.c. |
| Family construction form | M12 |
| Gender | female |
| Color contact carrier | black |
| Coding | B |
| No. of poles | 5 |
| PIN 1 | 5 V 2 |
| PIN 2 | A GN |
| PIN 3 | 0 V 2 |
| PIN 4 | B RD |
| PIN 5 | n.c. |
| Family construction form | 7/8" |
| Gender | male |
| Color contact carrier | black |
| No. of poles | 5 |
| PIN 1 | 0 V (UA) |
| PIN 2 | 0 V (US) |
| PIN 3 | PE |
| PIN 4 | 24 V DC (US) |
| PIN 5 | 24 V DC (UA) |
| Family construction form | 7/8" |
| Gender | female |
| Color contact carrier | black |
| No. of poles | 5 |
| PIN 1 | 0 V (UA) |
| PIN 2 | 0 V (US) |
| PIN 3 | PE |
| PIN 4 | 24 V DC (US) |
| PIN 5 | 24 V DC (UA) |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Murrelektronik:](#)

[55290](#)