

### Communicator



#### EtherNet/IP Scanners

Need to connect your EtherNet/IP device to another device running on different industrial networks? The Anybus Communicator has your back! No special cables, software, or training is required.

The EtherNet/IP Scanner from Anybus are designed to ensure reliable, secure, and high-speed data transfer between EtherNet/IP and different industrial Ethernet and Fieldbus networks. Very easy to install and deploy, the stand-alone gateways enable transparent data exchange allowing you to both bridge and integrate legacy equipment into modern high-performance networks.

#### High performance

Instant data transfer of up to 1500 bytes with hardware accelerated endian conversion (byte swap) enables you to take full advantage of high-speed industrial networks.



#### Cybersecurity

Designed to keep you safe from cyberattacks. Secure boot protects you against malicious software and a security switch adds physical protection to prevent unauthorized configuration changes.



#### Durability

Built using carefully selected industrial components and verified against industry standards. Proven network conformance thanks to the market-leading NP40 network processor.




#### User-friendly

You'll be up and running in no time, thanks to an intuitive web user interface, EDS file import, an Ethernet configuration cable, easy-to-understand documentation, and an effective housing design.



#### Product selection

Article nr	Control system	Device(s)
ABC3300	PROFIBUS	EtherNet/IP
ABC3313	PROFINET	EtherNet/IP
ABC3328	Modbus TCP	EtherNet/IP
ABC3361	EtherCAT	EtherNet/IP
ABC3390	Common Eth.*	EtherNet/IP
ABC3300EX	PROFIBUS	EtherNet/IP
ABC3390EX	Common Eth.*	EtherNet/IP



\*Common ethernet: select among EtherNet/IP, EtherCAT and PROFINET control system



Scan for more info  
about our products

### General

Dimensions with connectors (L x W x H)	98 x 27 x 144 mm / 3.85 x 1.06 x 5,67 in
Weight	150 grams, 0.33 lb
IP rating	IP20
Housing material	PC ABS, UL 94 VO
Mounting	DIN rail (35 * 7,5/15)
Operating temperature	-25 to 70° C, -13 to 158° F
Configuration	Web based via Ethernet configuration port
Industrial network connector(s)	2xRJ45 10/100 Mbit (daisy chaining) / DB9 (PROFIBUS)
Certification	CE, UKCA, UL ord loc (E214107), KC, RMC
MTBF	> 1 500 000 h, Telcordia Method I Case 3 at 30° C

### Power

Input voltage	12- 30 VDC
Current consumption	Typical 90mA @ 24V (2.2W) Maximal 3W
Power connector	3-pin plug with screw terminal
Protection	Reverse voltage protection and short circuit protection

### Network specifications

<b>EtherNet/IP Scanner</b>	
<ul style="list-style-type: none"> <li>- Transfer up to 1 500 bytes to EtherNet/IP devices</li> <li>- Transfer up to 1 500 bytes from EtherNet/IP devices</li> <li>- Total supported cyclic process data: 3000 bytes</li> <li>- Up to 32 adapters nodes</li> <li>- Drag and drop I/O configuration for data mapping</li> <li>- Transfer data cyclically or on data change</li> <li>- 1ms minimum cycle time for three adapters</li> <li>- Gateway latency &lt; 1ms</li> <li>- Endian conversion (without affecting latency)</li> <li>- Live list and data exchange control per adapter</li> </ul>	
<b>PROFINET IO Device</b>	<b>EtherCAT SubDevice</b>
<ul style="list-style-type: none"> <li>- Transfer up to 1 024 bytes from PROFINET</li> <li>- Transfer up to 1 024 bytes to PROFINET</li> <li>- Total supported cyclic process data: 2048 bytes</li> <li>- 1 ms minimum cycle time</li> <li>- Conformance class B, Real-Time (RT)</li> <li>- Network load robustness, Netload Class III</li> </ul>	<ul style="list-style-type: none"> <li>- Transfer up to 1 486 bytes from EtherCAT</li> <li>- Transfer up to 1 486 bytes to EtherCAT</li> <li>- Total supported process data: 2 972 bytes</li> <li>- EtherCAT SubDevice according to IEC 61158 Type 12 (ETG.1000)</li> <li>- Network cycle time down to 100 µs</li> <li>- Supports CANopen over EtherCAT</li> </ul>
<b>Modbus TCP Server</b>	<b>PROFIBUS DP Device (DPV1/DPV0)</b>
<ul style="list-style-type: none"> <li>- Transfer up to 1 500 bytes to Modbus TCP</li> <li>- Transfer up to 1 500 bytes from Modbus TCP</li> <li>- Total supported process data: 3 000 bytes</li> <li>- 4 connections</li> <li>- Function codes 01-06, 15-16, 23, 43/14</li> </ul>	<ul style="list-style-type: none"> <li>- Transfer up to 244 bytes to PROFIBUS</li> <li>- Transfer up to 244 bytes from PROFIBUS</li> <li>- Total supported process data: 488 bytes</li> <li>- Automatic baud rate detection up to 12 Mbit/s</li> <li>- Sync, Freeze and Watchdog</li> <li>- I&amp;M Ident numbers 0-31x</li> </ul>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HMS Networks:](#)

[ABC3300-A](#) [ABC3361-A](#) [ABC3328-A](#) [ABC3313-A](#)