


OA938AP Dual Voltage



AC Fans - 115, 230V
92mm x 92mm x 38mm (3.6" x 1.5")




Frame	Die Cast Aluminum, Black Finish	<u>Operating Temperature</u> -20°C ~ +70°C <u>Storage Temperature</u> -40°C ~ +100°C <u>Life Expectancy</u> 90,000 Hours (L10 at 45°C) Weight: 1 lbs.	
Impeller	PBT, UL94 V-0 Plastic		
Connection	4x Lead Wires, 22 AWG		
Motor	Shaded Pole Induction, Single Phase, Impedance Protected		
Bearing System	Dual Ball Bearings		
Dielectric Strength	1500VAC/min, <1mA		
Insulation Resistance	≥10MΩ @ 500V DC		


Part Number	Rated Voltage (Volts AC) 50 / 60Hz	Input Power (Watts) 50 / 60Hz	Voltage Range (Volts AC) 50 / 60Hz	Rated Speed (RPM) 50 / 60Hz	Airflow (CFM) 50 / 60Hz	Noise Level (dBA) 50 / 60Hz	Max. Static Pressure ("H ₂ O) 50 / 60Hz
OA938AP-11/22-1WB	115 / 230	11 / 9	100-120 / 200-240	2600 / 3100	41 / 50	33	0.16 / 0.22
OA938AP-11/22-2WB	115 / 230	7 / 5	100-120 / 200-240	2400 / 2500	36 / 39	27	0.13 / 0.16
OA938AP-11/22-3WB	115 / 230	4 / 3	100-120 / 200-240	2200 / 1900	29 / 26	24	0.12 / 0.10

*PQ Airflow Data specifications are for 60 Hz operation

Dual Voltage Wiring Diagram 115VAC



Dual Voltage Wiring Diagram 230VAC



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Orion Fans:](#)

[OA938AP-11/22-1WS](#) [OA938AP-11/22-1WB](#) [OA938AP-11/22-3WB](#) [OA938AP-11/22-3WS](#) [OA938AP-11/22-2WS](#)
[OA938AP-11/22-2WB](#) [OA938AP-1/2-3WB](#) [OA938AP-1/2-2WB](#) [OA938AP-1/2-1WB](#) [OA938AP-11/22-1TB](#) [OA938AP-11/22-2TB](#) [OA938AP-11/22-3TB](#)