


General Specifications

Motor Protection: Auto Restart / Polarity Protection
Insulation Resistance: 10M Ohm or over with a DC500V
Megger
Dielectric Withstand Voltage: AC 700V 1st
Allowable Ambient Temperature Range:
-10 degree C ~ +70 degree C (Operating)
-40 degree C ~ +70 degree C (Storage)
(non-condensing environment)

**order part 09225SS-24N-AA-D0 Sleeve
Bearing Fan DC Fans**




09225SS panel cut out




Material

Casing: Plastic (Black) UL94V-0
Impeller: Plastic (Black) UL94V-0
Lead Wire: UL1007, AWG26, +Red, -Black

09225SS characteristic curve



09225SS product drawing



Detailed Specifications

DC Fans

Expected Life:	40 degree C 50,000 Hours (L10)
DC Fan:	Sleeve Bearing Fan
Nominal Voltage:	24[V]
Operating Voltage Lower:	15[V]
Operating Voltage Upper:	27.6[V]
Current:	0.12[A]
Input Power:	2.9[W]
Speed:	3100[min^{-1}]
Max. Air Flow:	1.45[m ³ /min]
Max. Air Flow:	51.2[CFM]
Max. Static Pressure:	45[Pa]
Max. Static Pressure:	0.18[In H ₂ O]
Noise:	32[dB]
Mass:	102[g]
Fan Size:	92[mm]
Fan Width:	25[mm]
Life Expectancy L10:	40 degree C 50,000 Hours (L10)
Series:	09225SS

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[MinebeaMitsumi:](#)

[09225SS-24N-AA-D0](#)