



AUDIO
TECHNOLOGIES®

IEC CABLE CONNECTOR

AC power connector for high-current electrical appliances.

UL Listed



IO-C14

SPECIFICATIONS

PRODUCT

Gender: **Male**

Contacts: **3**

ELECTRICAL

Insulation Resistance: **>100MΩ**

Dielectric Strength: **2000V @ 60s**

Current Rating:

IEC 60320-3: 10A / 250V AC

UL 60320-3: 15A / 250V AC

ENVIRONMENTAL

Flammability Grade: **UL94 V-0**

Standards Compliance: **IEC 60320-3, UL 60320-3**

Working Temperature: **-40°C ~ +70° C (-40°F ~ +158°F)**

UL Listed (US/Canada): **E509788**

MECHANICAL

Mounting: **Cable Mount**

Max Cable O.D.: **9.2mm**

Max Conductor O.D.: **1.5mm**

Wiring: **Screw Terminals**

MATERIAL

Shell: **Thermoplastic**

Shell Finish: **Black**

Product specifications may change without prior notification

Io Audio Technologies® is a registered trademark of Knight Electronics, Inc.
10557 Metric Dr. Dallas, TX 75243 | 214-340-0265 | 800-323-2439 | Fax: 214-340-5870 |
www.ioaudiotecnologies.com



FEATURES & APPLICATIONS

IEC C14 AC power inlets are designed for single-phase AC applications and are rated for up to IEC 60320-3 current of 10A at 250V AC or UL 60320-3 current of 15A at 250V which makes them perfect for a variety of electronic equipment. Equipment includes computer components like the power supply, monitors, printers and other peripherals to video game consoles, instrument amplifiers, professional audio equipment and virtually all professional video equipment. It also includes enterprise-class servers, data centers, rack-mounted Power Distribution Units, Uninterruptible Power Supplies, large network routers, and network switches.

These connectors include several safety features to protect the user. They feature a pre-mating ground contact to ensure the circuit is properly grounded before the rest of the conductors make a connection, and they also feature a polarized design to prevent incorrect connections. These sturdy, locking plastic connectors offer durability that will ensure years of reliable service without interruption or fatigue. This cable mount connector features screw terminals and allows for a maximum cable O.D. of 9.2mm and a maximum conductor size of 1.5mm

PART NUMBER BREAKDOWN

IO-**C14**
IEC Class

STANDARDS & CLASSIFICATIONS



Product specifications may change without prior notification

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Io Audio:](#)

[IO-C14](#)