



## Part Number: D3C3743Q



### Electrical Specifications

|                        |             |
|------------------------|-------------|
| Frequency Range (GHz): | 37.0 – 43.0 |
| Isolation (dB):        | 14 MIN      |
| Insertion Loss (dB):   | 1.2 MAX     |
| VSWR:                  | 1.35:1 MIN  |
| Forward Power (W):     | 5 AVG       |
|                        | 30 PK       |


### Mechanical/Environmental Specifications

|                   |                            |
|-------------------|----------------------------|
| Connector Type:   | 2.4mm                      |
| Connector Body:   | Passivated stainless steel |
| Connector Pin:    | Gold plated copper         |
| Load Body:        | Brass                      |
| Magnetic Shunt:   | Nickel plated CRS          |
| Operational Temp: | -20°C to +65°C             |
| Weight (oz)       | 0.9 MAX                    |

### D3C3743Q Dimensions



### D3C3743Q-3 Dimensions



Dimensions are in inches  
Tolerance


XX ±0.03  
XXX ±0.010

| Type of Device                                                              | PN Suffix | Connector Configuration<br>Input / Output | PN Example |
|-----------------------------------------------------------------------------|-----------|-------------------------------------------|------------|
| Single Junction Circulator<br>3-Port Device<br><br>Port 1 / Port 2 / Port 3 | No Dash   | Female / Female / Female                  | D3C3743Q   |
|                                                                             | -1        | Male / Female / Female                    | D3C3743Q-1 |
|                                                                             | -2        | Female / Male / Female                    | D3C3743Q-2 |
|                                                                             | -3        | Male / Male / Male                        | D3C3743Q-3 |
|                                                                             | -4        | Female / Female / Male                    | D3C3743Q-4 |
|                                                                             | -5        | Male / Female / Male                      | D3C3743Q-5 |
|                                                                             | -6        | Male / Male / Female                      | D3C3743Q-6 |
|                                                                             | -7        | Female / Male / Male                      | D3C3743Q-7 |



## MEASURED DATA

Part Number: D3C3743Q, P1→P2, P3 Terminated with 50Ω, +25°C



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[DiTom:](#)

[D3C3743Q](#) [D3C3743Q-1](#) [D3C3743Q-2](#) [D3C3743Q-3](#) [D3C3743Q-4](#) [D3C3743Q-5](#) [D3C3743Q-6](#) [D3C3743Q-7](#)