

Product availability: Non-Stock - Not normally stocked in distribution facility

### Main

Device short name	XCSE
Enclosure type	Enclosure corrosion resistance indoor/outdoor Enclosure dust and damp proof indoor/outdoor

### Complementary

Line Rated Current	6 A
[Us] rated supply voltage	24 V
Actuator	Key
Cable entry	Conduit entry electromagnet connection
Contact operation	Slow-break, break before make
Contacts type and composition	1 NO staggered 2 NC
Depth	1.73 in
Enclosure material	Metal
Height	5.75 in
Installation direction	90° actuator supply
Locking options description	With locking of actuator, unlocking by key operated lock
Number of poles	3
Permissible voltage	<= 300 V AC
Pilot light	LED orange LED green
Connector type	Mini 9 pins

### Environment

Ambient air temperature for operation	-13...104 °F
IP degree of protection	IP67
NEMA degree of protection	NEMA 4/4X/12

### Ordering and shipping details

Category	18488 - INDUSTRIAL APPS-NON-NEGOTIABLE-T
Discount Schedule	T
GTIN	00785901443612
Nbr. of units in pkg.	1
Package weight(Lbs)	3
Returnability	N
Country of origin	US

## Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and
----- Substance 2	Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

## Contractual warranty

Warranty period	18 months
-----------------	-----------

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Telemecanique Sensors:](#)

[XCSE7313GD](#)