

MINIATURE SURFACE MOUNT RELAY For automotive applications 1 POLE - 25A

FTR-P6 Series

■ FEATURES

- Surface mount relays for automotive applications
- Miniature size (67% of the volume of FTR-P3 relays)
- High contact capacity with proven contact material (100,000 operations, 14V, 25A)
- Low coil power dissipation (800mW nominal achieved with state-of-the-art magnetic design)
- Semi low noise (average acoustic noise level: 60dB distance 5cm)
- Application examples: Power window, door lock, power seat, sunroof, wiper
- RoHS compliant

Please see page 7 for more information



■ Part Numbers

[Example] FTR-P6 G N 012 WA **
(a) (b) (c) (d) (e) (f)

(a)	Relay type	FTR-P6 : FTR-P6 series
(b)	Contact configuration	G : 1 form C
(c)	Contact gap	N : 0.25mm gap
(d)	Contact rated voltage	012 : 10..... 12VDC Coil rating table at page 3
(e)	Contact material	WA : Silver-tin oxide indium
(f)	Special type	None : Standard package DP : Dry package Others : To be assigned custom specification

Actual marking does not carry the type name: "FTR"

E.g.: Ordering code: FTR-P6GN012WA Actual marking: P6GN012WA

■ Specifications

Item	FTR-P6		Remarks / conditions	
Contact data	Configuration		1 form C	
	Material		Silver-tin oxide	
	Voltage drop		Max. 100 mV	At 1A, 12VDC (resistance)
	Contact rating		25A, 14VDC	Motor locked
	Max. carrying current		25A / 1h	25°C, nominal voltage applied to coil
	Max. inrush current		35A	
	Min. switching load *		1A, 6VDC	Reference
Coil	Coil power consumption		Approx. 0.8W	At rated coil voltage
	Operating temperature range		-40°C ~ +85°C	No frost
	Storage temperature range		-40°C ~ +100°C	No frost
	Operating humidity		45 to 85% RH	
Timing data	Operate		Max. 10ms	
	Release		Max. 5ms	
Life	Mechanical		Min. 1 x 10 ⁶ operations	
	Electrical		Min. 100 x 10 ³ operations	14VDC, 25A locked motor
Insulation	Insulation resistance		Min. 100MΩ at 500VDC	Initial
	Dielectric withstanding voltage	Open contacts	500VAC (50/60Hz), 1 minute	
		Coil contact	500VAC (50/60Hz), 1 minute	
Other	Vibration resistance	Misoperation	10 to 200Hz, 44m/s ² (4.5G), constant acceleration	
		Endurance	10 to 200Hz, 44m/s ² (4.5G), constant acceleration	
	Shock resistance	Misoperation	Min. 100m/s ² (11 ± 1ms)	
		Endurance	Min. 1,000m/s ² (6 ± 1ms)	
	Dimensions / weight		9.0 x 12.0 x 10.3 mm / approx. 3.3g	

*: Minimum switching loads mentioned above are reference values. Please perform the confirmation test with actual load before production since reference values may vary according to switching frequencies, environmental conditions and expected reliability levels.

Note: Care shall be taken on the heat generated on PC board when maximum carrying current exceeds 10A. Please perform the confirmation test with actual conditions.

■ Coil Data


Coil code	Rated Coil Voltage (VDC)	Coil Resistance +/-10%(Ω)	Must Operate Voltage* (VDC)	Must Release Voltage* (VDC)
010	10	125	6.5 (at 20°C) 8.2 (at 85°C)	0.8 (at 20°C) 1.0 (at 85°C)
012	12	180	7.3 (at 20°C) 9.2 (at 85°C)	1.0 (at 20°C) 1.3 (at 85°C)

Note: All values in the table are valid at 20°C and zero contact current, unless otherwise specified.

*: Specified operated values are valid for pulse wave voltage.


■ Dimensions

- Dimensions




*Dimensions of the terminals do not include thickness of pre-solder.

- Schematics (TOP VIEW)




- PC Board Mounting Hole Layout (TOP VIEW)



(): Reference value

Unit: mm

■ Packaging




■ Characteristic Data (Reference)


Life test (example)

- Test condition
25A 16VDC
motor lock
100,000 operations min.
0.5 sec. ON, 5.5 sec. OFF



- Test circuit



- Operate / release voltage




- Current wave form




FTR-P6 Series

- Test condition
Inrush current 20A,
16VDC motor free
400,000 operations min.
1.5 sec. ON, 2.0 sec. OFF



- Test circuit




- Operate / release voltage




- Current wave form





Coil temperature rise




Operating coil voltage range (FTR-P6GN012WA)




Vibration resistance characteristics Dual amplitude (mm)



Shock resistance characteristics




Shock application time: 6±1ms, half-sine wave
 Test condition: Coil energized and de-energized
 Shock direction: See diagram below
 Direction level: chatter > 1ms




○ : Break contact (coil de-energized)
 ● : Make contact (coil energized)


Distribution of operate/release voltage



Distribution of operate/release time



Distribution of contact resistance



CAUTIONS

- All values mentioned in this datasheet are provided under ideal conditions. Please perform the confirmation test before actual use.
- Reflow soldering is prohibited for flow soldering type.
- Do not use relays in the atmosphere with sulfide gas, chloride gas or nitric oxide. Contact resistance may increase.
- Do not use silicon or silicon-containing product or materials near relays. It may cause contact failure.

GENERAL INFORMATION

1. ROHS Compliance

- All relays produced by FCL Components are compliant with RoHS directive 2011/65/EU, including commission delegated directive 2015/863.

2. Recommended lead free solder condition


- Lead free solder plating on relay terminals is Sn-3.0Ag-0.5Cu, unless otherwise specified. This material has been verified to be compatible with PbSn assembly process.
- Recommended solder for assembly: Sn-3.0Ag-0.5Cu.

Solder by Soldering Iron:

Soldering Iron: 30-60W
Temperature: maximum 340-360°C
Duration: maximum 3 sec.

Reflow Solder Condition:

(Applicable only for reflow capable type)
Recommended reflow soldering profile
IRS (infrared reflow soldering)



We highly recommend that you confirm your actual solder conditions

3. Moisture Sensitivity

- Moisture Sensitivity Level standard is not applicable to electromechanical relays, unless otherwise indicated.

4. Tin Whiskers

- Dipped SnAgCu solder is known as presenting a low risk to tin whisker development. No considerable length whisker was found by our in house test.

Contact

Japan

FCL COMPONENTS LIMITED
Shinagawa Seaside Park Tower
12-4, Higashi-shinagawa 4-chome,
Tokyo 140 0002, Japan
Tel: +81-3-3450-1682
Email: fcl-contact@cs.fcl-components.com

North and South America

FCL COMPONENTS AMERICA, INC.
2055 Gateway Place Suite 480,
San Jose, CA 95110 USA
Tel: +1-408-745-4900
Email: fcai.components@fcl-components.com

Europe

FCL COMPONENTS EUROPE B.V.
Diamantlaan 25
2132 WV Hoofddorp, Netherlands
Tel: +31-23-556-0910
Email: info.fceu@cs.fcl-components.com

Asia Pacific

FCL COMPONENTS ASIA PTE LTD.
No. 20 Harbour Drive, #07-01B
Singapore 117612
Tel: +65-6375-8560
Email: fcal@fcl-components.com

China

FCL COMPONENTS (SHANGHAI) CO., LTD.
Unit 1105, Central Park - Jing An,
No.329 Heng Feng Road, Shanghai 200070,
China
Tel: +86-21-3253 0998
Email: fcsh@fcl-components.com

Web: www.fcl-components.com/en/

© 2024 FCL Components Limited. All rights reserved. All trademarks or registered trademarks are the property of their respective owners.

FCL Products are intended for general use, including without limitation, in personal, household and office environments, in buildings and for ordinary use in the industry. FCL Products are not intended to be used in applications where extremely high safety is required ("High Safety Required Applications"), such as, but not limited to, applications in nuclear facilities, in aircraft automatic flight control, in air traffic control, in mass transit system control, in missile launch system, in weapon systems, in medical equipment for life support or any application involving a direct serious risk of physical injury or death.

Please do not use FCL Products without securing the sufficient safety and reliability required for the High Safety Required Applications. In addition, FCL shall not be liable against the customer and/or any third party for any claims or damages arising in connection with the use of FCL Products in the High Safety Required Applications.

FCL warrants that its Products, if properly used and services, will conform to their specification and will be free from defects in material and workmanship for twelve months from delivery.

The implied warranties of merchantability and fitness for a particular purpose and all other warranties, representations and conditions, express or implied by statute, trade usage or otherwise, except as set forth in this warranty, are excluded and shall not apply to the Products delivered.

The contents, data and information in this datasheet are provided by FCL Components Limited as a service only to its user and only for general information purposes. The use of the contents, data and information provided in this datasheet is at the users' own risk.

FCL has assembled this datasheet with care and will endeavor to keep the contents, data and information correct, accurate, comprehensive, complete and up to date.

FCL Components Limited and affiliated companies do however not accept any responsibility or liability on their behalf, nor on behalf of its employees, for any loss or damage, direct, indirect or consequential, with respect to this datasheet, its contents, data, and information and related graphics and the correctness, reliability, accuracy, comprehensiveness, usefulness, availability and completeness thereof.

Nor do FCL Components Limited and affiliated companies accept on their behalf, nor on behalf of its employees, any responsibility or liability with respect to these datasheets, its contents, data, information and related graphics and the correctness, reliability, accuracy, comprehensiveness, usefulness, availability and completeness thereof. Rev. February 1, 2024.
