



Color Chart	
1 =	Black
2 =	Red
3 =	White
4 =	Yellow
5 =	Blue
6 =	Green




Specifications:

1. Insulation Resistance: 100MΩhms min. (initial)
2. Contact Resistance (initial): 30mΩhms max at 100mA(max) 1KHz.
3. Dielectric Withstand Voltage: AC 500V, 60Hz for 1 minute.
4. Insertion Force: 3Kgs max. Extraction Force: 0.08Kgs min.
5. Humidity Test: 40±2. 90~95%, 4B hours.

Color Index				
Part No.	Input X_1	Input X_2	Input X_3	Input X_4
RCJ-412211	Red	Red	Black	Black
RCJ-413344	White	White	Yellow	Yellow
RCJ-412233	Red	Red	White	White
RCJ-41 $X_1X_2X_3X_4$	Color X_1	Color X_2	Color X_3	Color X_4

Example: (Black, Red, White, Yellow)
 $RCJ-41X_1X_2X_3X_4 = RCJ-411234$

PC Board Layout
(Top View)

6	Input	PBT	4	See Color Index
5	Cover	ABS	2	Black Color
4	Base	ABS	1	Black Color
3	Terminal T	0.5t Brass	2	Silver Plated
2	Terminal D	0.5t Brass	2	Silver Plated
1	Earth Terminal (Barrel)	0.5t Brass	2	Nickel Plated
No.	Description	Material	Qty	Finish

Schematic	
L	R

CUDIVICES
6405 SW Rosewood St, Suite C
Lake Oswego, OR 97035
Phone: 877-323-3576
Website: www.cuidives.com

TITLE: RCA Jack, Quad 2x2, Rt. Angle, PCB Mount

PART NO.	RCJ-41XXXX	UNITS:	Millimeters
----------	------------	--------	-------------

DRAWN BY: Todd R. White	APPROVED BY:
----------------------------	--------------

SCALE:
1.5X

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Same Sky:](#)

[RCJ-412323](#)