

**SERIES:** TBL002B-350 | **DESCRIPTION:** TERMINAL BLOCK**FEATURES**

- 1~24 poles
- 45° angle with board
- interlocking (side)
- push button clamp
- 3.50 mm pitch
- UL and CE safety approvals

**SPECIFICATIONS**

parameter	conditions/description	min	typ	max	units
rated voltage (UL)	Use Group: B, D			300	V
rated current (UL)	Use Group: B, D			7	A
rated voltage (IEC)	Overvoltage Category/Pollution Degree: III/2			450	V
rated current (IEC)	Overvoltage Category/Pollution Degree: III/2			5	A
withstanding voltage			2,500		Vac
surge voltage				4,000	V
contact resistance				8	mΩ
insulation resistance	at 500 Vdc	500			MΩ
operating temperature		-40		105	°C
safety approvals	UL 1059, EN 60998-1:2004, EN 60998-2-1:2004				
flammability rating	UL94V-0				
RoHS	yes				

SOLDERABILITY

parameter	conditions/description	min	typ	max	units
hand soldering	for maximum 10 seconds	345	350	355	°C
wave soldering	for maximum 5 seconds	255	260	265	°C

PART NUMBER KEY



TBL002B - 350 - XX XX - 2XX			
Base Number	No. of Poles:	Body Color:	Push Button Color:
	01 07 13 19	BE = blue	BE = blue
	02 08 14 20	GR = green	GR = green
	03 09 15 21	OR = orange	OR = orange
	04 10 16 22	YL = yellow	YL = yellow
	05 11 17 23	*GY = gray	*GY = gray
	06 12 18 24	BK = black	BK = black
			WT = white

*Standard housing color is gray with gray push button. All other colors are subject to higher MOQ. Please inquire with Same Sky sales for details.

MECHANICAL DRAWING




units: mm
tolerance (per module):
 $X \leq 6.00$: ± 0.25 mm
 $6.00 < X \leq 30.00$: ± 0.40 mm
unless otherwise noted

DESCRIPTION	MATERIAL	PLATING/COLOR
housing	PA66 [UL94V-0]	
contacts	copper alloy	tin
elastic sheet	stainless steel	




A pin
when N is even, the number is N/2;
when N is odd, the number is (N-1)/2.

B pin
when N is even, the number is N/2;
when N is odd, the number is (N+1)/2.



Recommended PCB Layout
Top View



WIRE ASSEMBLY		
	UL	IEC
Wire Range	24~18 AWG	0.75 mm ²
Strip Length	8-9 mm	

This series is constructed of 1 pole modules where L is the total length, P is the pitch, and N is the number of poles.

N	01	02	03	04	05	06	07	08	09	10	11	12
L	5.00	8.50	12.00	15.50	19.00	22.50	26.00	29.50	33.00	36.50	40.00	43.50
B	--	3.50	7.00	10.50	14.00	17.50	21.00	24.50	28.00	31.50	35.00	38.50
N	13	14	15	16	17	18	19	20	21	22	23	24
L	47.00	50.50	54.00	57.50	61.00	64.50	68.00	71.50	75.00	78.50	82.00	85.50
B	42.00	45.50	49.00	52.50	56.00	59.50	63.00	66.50	70.00	73.50	77.00	80.50

REVISION HISTORY

rev.	description	date
1.0	initial release	11/12/2024

The revision history provided is for informational purposes only and is believed to be accurate.



Same Sky offers a one (1) year limited warranty. Complete warranty information is listed on our website.

Same Sky reserves the right to make changes to the product at any time without notice. Information provided by Same Sky is believed to be accurate and reliable. However, no responsibility is assumed by Same Sky for its use, nor for any infringements of patents or other rights of third parties which may result from its use.

Same Sky products are not authorized or warranted for use as critical components in equipment that requires an extremely high level of reliability. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

sameskydevices.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Same Sky:](#)

[TBL002B-350-04GY-2GY](#) [TBL002B-350-13GY-2GY](#) [TBL002B-350-10GY-2GY](#) [TBL002B-350-03GY-2GY](#) [TBL002B-350-07GY-2GY](#) [TBL002B-350-09GY-2GY](#) [TBL002B-350-12GR-2OR](#) [TBL002B-350-24GY-2GY](#) [TBL002B-350-09GR-2OR](#) [TBL002B-350-14GY-2GY](#) [TBL002B-350-06GY-2GY](#) [TBL002B-350-14GR-2OR](#) [TBL002B-350-23GY-2GY](#) [TBL002B-350-10GR-2OR](#) [TBL002B-350-19GR-2OR](#) [TBL002B-350-15GY-2GY](#) [TBL002B-350-23GR-2OR](#) [TBL002B-350-17GR-2OR](#) [TBL002B-350-04GR-2OR](#) [TBL002B-350-16GY-2GY](#) [TBL002B-350-21GR-2OR](#) [TBL002B-350-22GR-2OR](#) [TBL002B-350-05GR-2OR](#) [TBL002B-350-17GY-2GY](#) [TBL002B-350-12GY-2GY](#) [TBL002B-350-16GR-2OR](#) [TBL002B-350-21GY-2GY](#) [TBL002B-350-06GR-2OR](#) [TBL002B-350-07GR-2OR](#) [TBL002B-350-24GR-2OR](#) [TBL002B-350-02GY-2GY](#) [TBL002B-350-03GR-2OR](#) [TBL002B-350-11GY-2GY](#) [TBL002B-350-22GY-2GY](#) [TBL002B-350-02GR-2OR](#) [TBL002B-350-19GY-2GY](#) [TBL002B-350-08GR-2OR](#) [TBL002B-350-20GY-2GY](#) [TBL002B-350-20GR-2OR](#) [TBL002B-350-11GR-2OR](#) [TBL002B-350-18GR-2OR](#) [TBL002B-350-08GY-2GY](#) [TBL002B-350-13GR-2OR](#) [TBL002B-350-18GY-2GY](#) [TBL002B-350-05GY-2GY](#) [TBL002B-350-15GR-2OR](#)