



Wire _____ Tinned copper
 Gauge _____ AWG 28/7 0,089 mm²
 Voltage rating _____ 300 Vr.m.s
 Current rating _____ 2,1A at 25°C
 Capacity unbalanced _____ 45,9 pF/m at 1 MHz
 Impedance unbalanced _____ 105 Ω
 Propagation delay _____ 4,9 ns/m nominal
 Insulation material _____ PVC
 Temperature rating _____ -20°C (operating) to +105°C
 _____ -30°C (static)
 Flammability rating _____ Flame retardant VW1
 Insulation resistance _____ 100 MΩ/km
 Approval _____ UL AWM style 2651

09 18 015 7004	100 m (328 feet)
09 18 015 7001	30,48 m (100 feet)
Part number	Length per reel

				Det.	Name	 All Dim. in mm Orig. Size DIN A 4	SEK 18 flat cable 15 poles	Maßstab/ Scale
			Detail.	20/10/05	JMDR			10:1
			Insp.					
			Stand.					
EC01360	19/02/10	SC	HARTING EURL			TB 09 18 015 700X	Blatt/ Page	
33246	20/10/05	JMDR	F-95972 Paris				1 / 1	
Mod.	Det.	Name					Sub.	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09180157004](#) [09180157001](#)