



assembly aid enclosed

SW15
width across
flats 15

A (2:1)
contact face acc. to
IEC 61076-2-101

Ø16,4

SW14
width across
flats 14

SW15
width across
flats 15

complete length when assembled app. 40.5

order contacts separately

Cable description	Cable diameter	Wire gauge	P/N contact	P/N Crimping insert	P/N Crimping Tool	P/N Mounting tool
RADOX DATABUS 120 OHM 2x0,5mm2+0,5mm2 Huber&Suhner: 84138531	7,8mm	AWG 24-20 AWG 22-18	09 67 000 8576 09 67 000 3576	0999 000 0653	0999 000 0647	0999 000 0639

	All Dimensions in mm Original Size DIN A4		Scale 1:1	Free size tol.		Ref.
	All rights reserved Department EC PD - RO		Created by STOICA	Inspected by AVRAM	Standardisation HOFFMANN	Sub.
HARTING Electronics GmbH D-32339 Espelkamp			Title M12 4-poles D-coded crimpflange male			Date 2017-11-03
			Type TB			State Final Release
			Number 21038811412			Doc-Key / ECM-Nr. 100692365/UGD/002/C 500000127343
						Rev. C
						Page 1/1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[21038811412](#)