

# SILICON MULTI-EPITAXIAL NPN TRANSISTOR

## BUX23

- High Current, Fast Switching.
- Hermetic Metal TO3 Package.
- Ideally suited for Motor Control and Power Switching Circuits
- Screening Options Available



### ABSOLUTE MAXIMUM RATINGS ( $T_C = 25^\circ\text{C}$ unless otherwise stated)

$V_{CBO}$	Collector – Base Voltage		400V
$V_{CEX}$	Collector – Emitter Voltage	$V_{BE} = -1.5V$	400V
$V_{CEO}$	Collector – Emitter Voltage		325V
$V_{EBO}$	Emitter – Base Voltage		7V
$I_C$	Continuous Collector Current		30A
$I_{CM}$	Peak Collector Current	$t_p = 10ms$	40A
$I_B$	Base Current		6A
$P_D$	Total Power Dissipation at	$T_C = 25^\circ\text{C}$	250W
		Derate Above $25^\circ\text{C}$	1.67W/ $^\circ\text{C}$
$T_J$	Junction Temperature Range		-65 to $+175^\circ\text{C}$
$T_{stg}$	Storage Temperature Range		-65 to $+175^\circ\text{C}$

### THERMAL PROPERTIES

Symbols	Parameters	Min.	Typ.	Max.	Units
$R_{\theta JC}$	Thermal Resistance, Junction To Case			0.6	$^\circ\text{C/W}$

Semelab Limited reserves the right to change test conditions, parameter limits and package dimensions without notice. Information furnished by Semelab is believed to be both accurate and reliable at the time of going to press. However Semelab assumes no responsibility for any errors or omissions discovered in its use. Semelab encourages customers to verify that datasheets are current before placing orders.



# SILICON MULTI-EPITAXIAL NPN TRANSISTOR BUX23

## ELECTRICAL CHARACTERISTICS ( $T_C = 25^\circ\text{C}$ unless otherwise stated)

Symbols	Parameters	Test Conditions	Min.	Typ	Max.	Units
$V_{(BR)CEO}^{(1)}$	Collector-Emitter Breakdown Voltage	$I_C = 0.2\text{mA}$	325			V
$V_{(BR)EBO}$	Emitter-Base Breakdown Voltage	$I_E = 50\text{mA}$	7			
$I_{CEO}$	Collector Cut-Off Current	$V_{CE} = 260\text{V}$ $I_B = 0$			3	mA
$I_{CEX}$	Collector Cut-Off Current	$V_{CE} = 400\text{V}$ $V_{BE} = -1.5\text{V}$			3	
		$T_C = 125^\circ\text{C}$			12	
$I_{EBO}$	Emitter Cut-Off Current	$V_{EB} = 5\text{V}$ $I_C = 0$			1.0	
$V_{CE(sat)}^{(1)}$	Collector-Emitter Saturation Voltage	$I_C = 8\text{A}$ $I_B = 1.6\text{A}$		0.2	0.8	V
		$I_C = 16\text{A}$ $I_B = 3.2\text{A}$		0.35	1.0	
$V_{BE(sat)}^{(1)}$	Base-Emitter Saturation Voltage	$I_C = 16\text{A}$ $I_B = 3.2\text{A}$		1.15	1.5	
$h_{FE}^{(1)}$	Forward-current transfer ratio	$I_C = 8\text{A}$ $V_{CE} = 4\text{V}$	12		60	
		$I_C = 16\text{A}$ $V_{CE} = 4\text{V}$	8			

## DYNAMIC CHARACTERISTICS

$f_T$	Transition Frequency	$I_C = 2\text{A}$ $V_{CE} = 15\text{V}$ $f = 10\text{MHz}$	8			MHz
$t_{on}$	Turn-On Time	$I_C = 16\text{A}$ $I_{B1} = 3.2\text{A}$		0.55	1.3	$\mu\text{s}$
$t_s$	Storage Time	$I_C = 16\text{A}$ $I_{B1} = -I_{B2} = 3.2\text{A}$		1.7	2.5	
$t_f$	Fall Time			0.26	1.2	

### Notes

(1) Pulse Width  $\leq 380\mu\text{s}$ ,  $\delta \leq 2\%$



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cicor:](#)

[BUX23](#)