

TITLE. EXTENDER 45°

METRIC

EPF 313G




TABLE I

SHELL SIZE			Ø B MAX				F	G	Ø E MAX	
A	F & L	H	A	F	L	H	MAX	MAX	A & F	H
08	08	09	15.50	15.50	16.50	17.70	11.45	14.00	6.85	8.55
10	10	11	19.00	19.00	19.60	21.00	11.45	14.00	9.53	11.80
12	12	13	22.00	22.00	22.60	24.00	12.70	15.25	12.98	14.70
14	14	15	25.00	25.00	25.90	27.50	14.00	16.50	14.86	17.90
16	16	17	28.50	29.50	29.20	31.00	15.20	17.80	18.03	21.05
18	18	19	30.50	30.50	31.20	32.50	16.50	19.05	20.04	23.75
20	20	21	33.50	33.50	34.50	37.50	16.50	20.30	23.22	26.90
22	22	23	36.70	36.70	37.60	40.30	17.80	21.60	26.39	30.10
24	24	25	40.00	40.00	40.60	42.00	19.05	22.25	29.31	33.25
									'A' DESIGNATOR	
28	-	-	50.00	-	-	-	24.00	28.00	35.28	
32	-	-	57.90	-	-	-	25.50	29.70	41.30	
36	-	-	64.30	-	-	-	26.50	30.00	46.99	

PART No. DEVELOPMENT

EXAMPLE

328 H H 131 NF 09

PRODUCT SERIES

CONNECTOR DESIGNATOR

A F L OR H

ANGULAR FUNCTION

H = 45° SOLID

BASIC No.

FINISH

△

SHELL SIZE

TABLE I

NOTES

△ SEE STD-001 (COMMON ACCESSORY INTERFACE DATA)

2. MATERIAL - AL ALLOY

△ FINISH

STANDARD FINISH:

NF - CAD PLATE/OLIVE DRAB OVER ELECTROLESS NICKEL (500 HR SALT SPRAY)

M - ELECTROLESS NICKEL

SEE STD-001 FOR ALTERNATIVES

CONFORMS TO WESTLANDS SPECIFICATION EE068 ISSUE 9

REVISION	A	B	C	D	E	F	G			
DCO	RELEASE	90-404	90-453	2651	3201	10130	10147			
DATE	JUL 92	AUG 92	JAN 93	FEB 98	MAY 99	FEB 12	MAR 12			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Glenair:

[328HH131NF15](#)