

## Han HPR SP2-PFT/TE-SCL-M40



Image is for illustration purposes only. Please refer to product description.

Part number	19 40 021 1113
Specification	Han HPR SP2-PFT/TE-SCL-M40
HARTING eCatalogue	<a href="https://b2b.harting.com/19400211113">https://b2b.harting.com/19400211113</a>

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han® HPR
Type of hood/housing	Panel feed through housing

### Version

Size	SP2
Version	Top entry
Number of cable entries	1
Cable entry	1x M40
Locking type	Screw locking
Field of application	Hoods/housings for harsh outdoor environments

### Technical characteristics

Tightening torque	6 Nm Locking screw
	6 Nm Fixing screws
	15 Nm Retaining ring
Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP65
	IP68
	IP69 / IPX9K acc. to ISO 20653
Type rating acc. to UL 50 / UL 50E	4
	4X
	12



**Pushing Performance**  
Since 1945

## Technical characteristics

Thickness of the panel  $\geq 2$  mm

## Material properties

Material (hood/housing)	Aluminium die-cast Corrosion resistant
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 9005 (jet black)
Material (seal)	NBR

## Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
Approvals	CE DNV GL

## Commercial data

Packaging size	1
Net weight	399 g
Country of origin	China
European customs tariff number	85389099
GTIN	5713140831353
ETIM	EC000437
eCl@ss	27440202 Shell for industrial connectors

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[19400211113](#)