

## M12 A-cod 4-pol st /st m /f PVC 5.00m



Image is for illustration purposes only. Please refer to product description.

Part number	C2 13 200 0000 0003
Specification	M12 A-cod 4-pol st /st m /f PVC 5.00m
HARTING eCatalogue	<a href="https://b2b.harting.com/C213200000000003">https://b2b.harting.com/C213200000000003</a>

### Identification

Category	System cabling
Series	Circular connectors M12
Element	Cable assemblies
Specification	Pre-assembled on both sides
Connector 1	M12 A-coding Male Straight Overmoulded
Connector 2	M12 A-coding Female Straight Overmoulded
Type of cable	Copper cable (round)

### Version

Cable length	5 m
Number of cores	4
Core structure	4x 0.34 mm <sup>2</sup>
Termination method	Crimp termination
Shielding	Unshielded
Coding	A-coding

### Technical characteristics

Rated current	4 A
Rated voltage	250 V
Limiting temperature	-25 ... +80 °C moved -40 ... +80 °C unmoved



Pushing Performance  
Since 1945

## Technical characteristics

Degree of protection acc. to IEC 60529	IP65 / IP67 mated condition
Cable diameter	4.9 mm

## Material properties

Material (cable)	PVC
Colour (cable)	RAL 7040 (Window grey)
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

## Specifications and approvals

Specifications	IEC 61076-2-101
	UL 1581
	IEC 60332-2-2 Flame retardancy
UL / CSA	UL in preparation
Approvals	CE

## Commercial data

Packaging size	2
Net weight	205 g
Country of origin	Germany
European customs tariff number	85444290
GTIN	5713140512801
ETIM	EC001855
eCl@ss	27060311 Assembled sensor actuator-line

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[C2132000000003](#)