

RVPX-J08EXX		DOCUMENT NO.
REV. A	SHEET 1 OF 2	
REVISIONS M		
LTR	DESCRIPTION	DATE
A	INITIAL RELEASE	11-FEB-16







TABLE 1

PLATING THICKNESS AND MATERIAL BY PART NUMBER			
PART NUMBER	GOLD IN CONTACT AREA	COMPLIANT	NICKEL OVERALL
RVPX-J08EM1	50 μ-INCH MIN	50 μ-INCH MIN TIN	50 μ-INCH MIN
RVPX-J08EM2	50 μ-INCH MIN	50 μ-INCH MIN TIN-LEAD	50 μ-INCH MIN
RVPX-J08EC1	30 μ-INCH MIN	50 μ-INCH MIN TIN	50 μ-INCH MIN
RVPX-J08EC2	30 μ-INCH MIN	50 μ-INCH MIN TIN-LEAD	50 μ-INCH MIN




- NOTES:
- HOUSING: GLASS FILLED LCP, UL94 - V0
CONTACT: Cu ALLOY
 - PTH CALLOUT
TYPICAL HOLE
Ø0.63-.67 DRILL
Ø0.56 ±.05 FINISH HOLE
Ø1.02 PAD
 - SEE TABLE 1 FOR PART NUMBER AND FINISHES
 - ADDITIONAL CONNECTOR-SIDE KEEPOUT AREA
REQUIRED IF CONNECTOR-SIDE EXTRACTION
TOOL IS TO BE USED.

THE USE OF THIS DOCUMENT IS UNLIMITED. HOWEVER, DOCUMENTS REFERENCED HEREON MAY CONTAIN LIMITED RIGHTS DATA.		
DOCUMENT NO. RVPX-J08EXX	SHEET 1 OF 2	REV. A

N/A	PRO/ENGINEER INFORMATION Pro/e Model Used: RVPX-J08EXX.ASSEM Drawing Name: RVPX-J08EXX
NEXT ASSEMBLY	

UNLESS OTHERWISE SPECIFIED		SPECIFICATIONS		POS	QTY	PART NUMBER	DESCRIPTION	NOTE
LINEAR DIMENSIONS ARE IN MILLIMETERS TOLERANCES: .XXXX = ± ANGLES= ±2° .XXX = ± .XX = ±.1 .X = ±.13 DIM.& TOL. PER ASME Y14.5M; DRM PER MIL-DTL-31000; OTHER Amphenol Sds. PER 9-3800 LEGENDS: =FLAG NOTE CALL OUT REFERENCE ONLY		MATERIAL SPEC.		PARTS LIST				
		N/A		APPROVALS				
PROCESS SPEC.		9-3895 9-3856-5		THIRD ANGLE PROJECTION				
				AMPHENOL CORPORATION 40-60 DELAWARE AVENUE SIDNEY, N.Y. 13838 CONNECTOR ASSEMBLY, BACKPLANE VERTICAL RECEPTACLE, 8 POS., LEFT END RVPX				
				SIZE C CAGE CODE 77820 DOCUMENT NO. RVPX-J08EXX REV. A				
				SCALE: 5.0 REF. NONE SHEET 1 OF 2				

REAR TRANSITION MODULE APPLICATION



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[RVPX-J08EM2](#) [RVPX-J08EM1](#) [RVPX-J08EC1](#) [RVPX-J08EC2](#)