


NOTES:


1. METALSHELLS: STEEL; min. 315µm TIN over 40-80µm NICKEL
2. INSULATORS: PBT GF UL 94 V-0, GREEN
3. HIGH POWER CONTACTS 20A: COPPER ALLOY
PLATING, MATING AREA: GOLD FLASH over NICKEL
PLATING, TERMINATION SIDE: 160-240µm TIN over 80µm NICKEL
4. SIGNAL CONTACTS: COPPER ALLOY;
PLATING: GOLD FLASH over NICKEL
5. METAL BRACKETS: ZINC DIE CAST; 300µm COPPER/40-120µm NICKEL/120-200µm TIN
6. THREADED INSERTS: COPPER ALLOY; min. 200µm TIN over 80µm NICKEL
7. FIXING-PLATES: PBT GF UL 94 V-0, BLACK
8. P.C.B. HOLE DRILLINGS ON SHEET 2
9. MAXIMUM TORQUE VALUE FOR THREAD: 6 in.LB
10. CONNECTOR IS PART MARKED: **13-001023 CONEC ABC**

Directive 2002/95/EC RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH DO NOT ALTER CAD DRAWING BY HAND	tolerance		dim. in mm		scale:	2:1	
					material:	see notes	
	date	name		title:			
	drawn	13.03.14	Henneboel		D-SUB COM. DUAL PORT		
	appd.	17.03.14	Lehmenkühler		19,05mm / Male 7W2P reverse / Male 7W2P with threaded insert, metal bracket, fixing-plate		
	norm			dwg no:			
	d-old			13K1A4610			
	a	Original			DIN-A3		
	rev.	description	date	name	part no:		sh: 1/2
					13-001023		





THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH DO NOT ALTER CAD DRAWING BY HAND				tolerance		scale: 4:1
				dim. in mm		material: see sheet 1
				date	name	title: P.C.B. HOLE DRILLINGS D-SUB Combination Dual Port 19,05mm Male 7W2P reverse /Male 7W2P
				drawn	13.03.14 Henneboel	
				appd.	17.03.14 Lehmenkühler	
			norm		dwg no:	
			d-old		DIN-A3	
			rev.	description	date	name
			a	Original		
			CONEC [®]			part no: SEE SHEET 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[13-001023](#)