

A

A

B

B

mat'l. code		surface		tolerance		projection		product family	
		ISO 1302		ISO 406/ISO 1101		mm		MINITEK HPL577	
ltr		ecn no		dr		date		title	
								MINITEK II R/A HEADER	
								dwg no	
								sheet 1 of 1 size	
								10138622	
								A4	
								type	
								Product Customer Drawing	
sheet index		revision sheet		A					
1		1							



1 | 2



3 |

4


PRODUCT NO	POS	CONTACT AREA	SOLDER AREA
10138622-001LF	2 X 3	0.76um Au OVER Ni	2.54um MATTE Sn

NOTES:

- MATERIAL:  
BODY : HIGH TEMPERATURE PLASTIC UL 94V-0 BLACK  
PIN: COPPER ALLOY  
PLATING: SEE SHEET 2 TABLE
- 10138622-001LF: STANDARD PACKAGING USED BAG.  
10138622-001TRLF: PACKAGING USED TAPE AND REEL WITH CAP.
- THE HOUSING WILL WITHSTAND EXPOSURE TO 255°C PEAK TEMPERATURE FOR 10 SECONDS IN A CONVECTION, INFRA-RED OR VAPOR PHASE REFLOW OVEN.
- THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.57MM MINIMUM THICK CIRCUIT BOARD.
- THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.



WITH PLASTIC CAP



mat'l. code		surface	tolerance	projection	product family
		ISO 1302	ISO 406/ISO 1101		MINITEK HPL577
ltr	ecn no	dr	date	tolerances unless otherwise specified	title
				mm	MINITEK II R/A HEADER
				angles	
				0±2'	scale 1:1
		dr	Laurence Zang	160315	dwg no
		engr	Laurence Zang	160315	sheet 1 of 1 size
		chr	Tim Yao	160315	10138622
		appd	Tim Yao	160315	A4
sheet index	revision sheet	A			type
	2				Product Customer Drawing

1 |

2 |

3 |

4

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI / Amphenol:](#)

[10138622-001LF](#)