


FCI PART NO.

10121546-P0030YYLF

WIRING LIST

CN1	CN2	WIRE COLOR
1	15	ORANGE
2	14	
3	13	WHITE/ORANGE
4	12	YELLOW
5	11	
6	10	YELLOW/BLACK
7	9	
8	8	BLACK
9	7	BLACK/WHITE
10	6	
11	5	BROWN
12	4	
13	3	RED
14	2	
15	1	RED/WHITE



NOTES:

1. MATERIAL: SEE BOM ON SHEET 1.
2. THIS DIMENSION IS A FINISHED PRODUCT LENGTH.
3. ALL CABLE ASSEMBLIES SHALL BE TESTED 100% FOR CONTINUITY AS DEFINED IN WIRING LIST.
4. UNLESS OTHERWISE SPECIFIED ALL CABLE ASSEMBLIES SHALL BE TESTED:
 HI-POT: DC 300V/10ms
 DIELECTRIC RESISTANCE: 10M Ohms MIN.
 CONNECTION RESISTANCE: 4 Ohms MAX.
5. LEAD FREE PRODUCTS MEET EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.

2	EA	LABEL: WIDTH=9.5mm, BLACK TEXT.	5
A/R	M	HEAT SHRINK TUBE: OD=8.0mm, COLOR:BLACK	4
A/R	M	CABLE: 28AWG*5P+AL FOIL, UL2586, OD=7.8mm, COLOR:BLACK	3
18	EA	TERMINAL: 0.76um GOLD PLATING, FCI P/N:77138-101LF	2
2	EA	HOUSING: 2.0PITCH, 15PIN, COLOR:BLACK, FCI P/N:90312-015LF	1
Q'TY	UNIT	DESCRIPTION	ITEM

spec ref	See Notes			dr	Carl Wang	2015-01-19	projection	MM	size	A3	scale	N/A	
tolerance std	TOLERANCES UNLESS OTHERWISE SPECIFIED			eng	Carl Wang	2015-01-19			ecn no		rel level		
surface	linear	0.X	±	chr	Guo-Feng Jin	2015-01-19			product family		title		
		0.XX	±	appr	Guo-Feng Jin	2015-01-19			MINITEK CABLE ASSEMBLY		dwg no	10121546-P0030YYLF	rev
	angular	0°	±°	www.fci.com		cat. no.	Product - Customer Drw		sheet 1 of 1				



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI / Amphenol:](#)

[10121546-P0030YYLF](#)